

OSCILLOSCOPE PROBE CP2350



Characteristic

- The oscilloscope probe CP series is the most widely used oscilloscope probe. At the same time, it is the most durable and economical probe. There are no active components such as transistors or amplifiers in passive probes, so there is no need to power the probe.

Model	CP2350
Attenuation Ratio	1X,10X
Accuracy	±1%
Bandwidth	1X:DC-6MHz 10X:DC-350MHz
Rise time	1X:58ns 10X:1ns
Input impedance	1X:1MΩ 10X:10MΩ
Input capacitance	1X:46pF 10X:13pF
Working voltage	1X:300V 10X:600V
Working Temperature	0~50°C
Cable length	1.2m
Weight	90g

● ACCESSORIES



Insulated
Tip



Measuring
Tip



Spring
Hook



Adjustment
Tool



Integrated
Circuit Frontier



The Probe Tip
Is Grounded



PL-15



Channel
Identifier

GUANGZHOU PINTECH CO.,LIMITED

Web:www.pintech.com.cn

Tel:86-20-82510899

E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.