

Differential Probe DP-220



Characteristic

- 2% accuracy.
- Adaptor power supply.
- Standard BNC interface, compatible with any brand's oscilloscope.

Model	DP-220
Bandwidth(-3dB)	DC-200MHz
Attenuation Ratio	10X,100X
Accuracy	±2%
Rise Time	≥1.75ns
Input differential Vp-p	10X:52V; 100X:520V
Input differential V AC RMS	183V
Input differential V DC	10X:26V; 100X:260V
Common mode voltage(rms)	91.5V
Input Impedance	0.5MΩ//2pF(Single-ended); 1MΩ//1pF(Both ends)
Noise RMS	10X:≤50mV rms; 100X:≤100mV rms
5MHz Bandwidth limited	Switchable:Full/5MHz
Oscilloscope input impedance	1MΩ
Power adaptor	External 5V DC power supply
CMRR(Tyical)	60Hz:>80dB; 100Hz:>60dB; 1MHz:>50dB
Temperature	0~50°C
Humidity	10~85%RH
Weight	285g
Dimension(L*W*H)	175×68×28mm

● ACCESSORIES



Adapter



USB



BP-256N



BP-276N



BP-366A



BP-286N



Plug Adaptor

GUANGZHOU PINTECH CO.,LTD

Web:www.pintech.com.cn

Tel:020-82510899

E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.