


Features

- Power Dissipation: 300 mW
- Zener Voltage Tolerance: $\pm 2\%$

PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



Absolute Maximum Ratings ($T_a = 25^\circ\text{C}$)

Parameter	Symbol	Value	Unit
Total Power Dissipation	P_{tot}	300	mW
Junction Temperature	T_j	150	$^\circ\text{C}$
Storage Temperature Range	T_{stg}	- 55 to + 150	$^\circ\text{C}$

Characteristics at $T_a = 25^\circ\text{C}$

Parameter	Symbol	Max.	Unit
Thermal Resistance Junction to Ambient Air	$R_{\theta\text{JA}}$	417	$^\circ\text{C/W}$
Forward Voltage at $I_F = 10\text{ mA}$	V_F	0.9	V

WPMtek

Typical Characteristics



Type	Zener Voltage Range ¹⁾			Dynamic Impedance		Reverse Leakage Current	
	V_{Znom} V	I_{ZT} mA	for V_{ZT} V	Z_{ZT} (Max.) Ω	at I_{ZT} mA	I_R (Max.) μA	at V_R V
MM3Z2B4	2.4	5	2.352...2.448	100	5	120	1
MM3Z2B7	2.7	5	2.646...2.754	110	5	120	1
MM3Z3B0	3.0	5	2.94...3.06	120	5	50	1
MM3Z3B3	3.3	5	3.234...3.366	130	5	20	1
MM3Z3B6	3.6	5	3.528...3.672	130	5	10	1
MM3Z3B9	3.9	5	3.822...3.978	130	5	5	1
MM3Z4B3	4.3	5	4.214...4.386	130	5	5	1
MM3Z4B7	4.7	5	4.606...4.794	130	5	2	1
MM3Z5B1	5.1	5	4.998...5.202	130	5	2	1.5
MM3Z5B6	5.6	5	5.488...5.712	80	5	1	2.5
MM3Z6B2	6.2	5	6.076...6.324	50	5	1	3
MM3Z6B8	6.8	5	6.664...6.936	30	5	0.5	3.5
MM3Z7B5	7.5	5	7.35...7.65	30	5	0.5	4
MM3Z8B2	8.2	5	8.036...8.364	30	5	0.5	5
MM3Z9B1	9.1	5	8.918...9.282	30	5	0.5	6
MM3ZB10	10	5	9.8...10.2	30	5	0.1	7
MM3ZB11	11	5	10.78...11.22	30	5	0.1	8
MM3ZB12	12	5	11.76...12.24	35	5	0.1	9
MM3ZB13	13	5	12.74...13.26	35	5	0.1	10
MM3ZB15	15	5	14.7...15.3	40	5	0.1	11
MM3ZB16	16	5	15.68...16.32	40	5	0.1	12
MM3ZB18	18	5	17.64...18.36	45	5	0.1	13
MM3ZB20	20	5	19.6...20.4	50	5	0.1	15
MM3ZB22	22	5	21.56...22.44	55	5	0.1	17
MM3ZB24	24	5	23.52...24.48	60	5	0.1	19
MM3ZB27	27	5	26.46...27.54	70	2	0.1	21
MM3ZB30	30	5	29.4...30.6	80	2	0.1	23
MM3ZB33	33	5	32.34...33.66	80	2	0.1	25
MM3ZB36	36	5	35.28...36.72	90	2	0.1	27
MM3ZB39	39	2.5	38.22...39.78	100	2	2	30
MM3ZB43	43	2.5	42.14...43.86	130	2	2	33
MM3ZB47	47	2.5	46.06...47.94	150	2	2	36
MM3ZB51	51	2.5	49.98...52.02	180	2	1	39
MM3ZB56	56	2.5	54.88...57.12	180	2	1	43
MM3ZB62	62	2.5	60.76...63.24	200	2	0.2	47
MM3ZB68	68	2.5	66.64...69.36	250	2	0.2	52
MM3ZB75	75	2.5	73.5...76.5	300	2	0.2	57

¹⁾ V_Z is tested with pulses (20 ms).

PACKAGE OUTLINE

Plastic surface mounted package; 2 leads

SOD-323



UNIT	A	b _p	C	D	E	H _E	A ₁	L _p
mm	1.20 0.90	0.40 0.25	0.15 0.10	1.80 1.60	1.35 1.15	2.80 2.30	0.10 0.01	0.50 0.20

WPMtek reserves the right to make changes to the product specification and data in this document without notice. WPMtek makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does WPMtek assume any liability arising from the application or use of any products or circuits, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Any enquiry, please write to sales@wpmtek.com for further information.