

High Frequency Current Probe PT-3215A



Characteristic

- Easy to use and accurate AC/DC current measurements.
- DC-2MHz bandwidth.
- Jaw diameter 20mm.
- High accuracy, 1% DC gain error.
- Split-core structure for easy circuit connection.
- Low noise and DC drift.
- Amplifier not required
- power adapter included.

Model	PT-3215A
Bandwidth(-3dB)	DC-2MHz
AC current	1500Ap-p
Current RMS	500A rms
DC current	750A
Minimum current	50mA
Accuracy	50X:±1%+1mV; 500X:±1%+1mV
Conversion Ratio	20mV/A(50X); 2mV/A(500X)
Measuring range	50X:50mA~125Apeak; 500X:125A~750Apeak
Noise rms	50mA
Rise time	175ns
Coupled mode	AC/DC
Power supply	12V
Clamp Dia	20mm
Operation temp	0~50°C
Operation humidity	20~75%RH
Dimension(L×W×H)	Probe pliers 151.9×64.7×31.8mm
Weight	Approximately 389g

● ACCESSORIES



Adapter



Power cord



BP-250N



Grounding Wire

GUANGZHOU PINTECH CO.,LIMITED

Web:www.pintech.com.cn

Tel:86-20-82510899

E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.