






X	
PART NO	vigor
2	G2
3	G3
4	G4
5	G5
6	G6
7	G7
8	G8



Specification:
1.Rating: DC 30V 50mA
2.Travel: 2.5±0.1mm
3.Operating Force:A-B 250gf±100gf
B-A 250gf±100gf
4.Contact Resistance:100mΩ Max
5.Life:10,000 Cycles Min



4	TERMINAL	BRASS STRIP
3	TERMINAL BASE	PHENOLIC RESIN
2	FRAME	STEEL STRIP
1	KNOB	POM
NO.	PART NAME	MATERIAL

APPROVALS		DATE		DRAWING NO.	
DRAWN	G.M.Chen	2025/5/4	TITLE: VERTICAL SLIDE SWITCHES		SHEET 1 OF 1
CHECKED			SCALE: 1:1		PROJ. 1 OF 1
APPROVALS			PART NO. SK-22F03-GX		
TOLERANCES ARE		30±0.1	±0.30	ANGLE	UNIT: mm
		10±0.10	±0.20		
		5±0.10	±0.15	±2°	
ECN NO.	REV.	DATE.	DESCRIPTION.		CHANGE.
	A		NEW		