

Differential Probe DP-35



Characteristic

- 2% accuracy.
- Adaptor power supply.
- Standard BNC interface, compatible with any brand's oscilloscope.

Model	DP-35
Bandwidth(-3dB)	10X:DC-25MHz; 100X:DC-35MHz
Attenuation Ratio	10X,100X
Accuracy	±2%
Rise Time	≥10ns
Input differential Vp-p	10X:160V; 100X:1600V
Input differential V AC RMS	560V
Input differential V DC	10X:80V; 100X:800V
Common mode voltage(rms)	280V
Input Impedance	4.5MΩ//3.4pF(Single-ended); 9MΩ//1.7pF(Both ends)
Noise RMS	≤1mV rms
Oscilloscope input impedance	1MΩ
Power adaptor	5V adapter
CMRR(Typical)	60Hz:>80dB; 100Hz:>60dB; 1MHz:>50dB
Temperature	0~50°C
Humidity	10~85%RH
Weight	250g
Dimension(L*W*H)	195×55×30mm

● ACCESSORIES



5V Adapter



BP-250



BP-256



BP-276N



BP-356N

GUANGZHOU PINTECH CO.,LTD

Web:www.pintech.com.cn

Tel:020-82510899

E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.