

High Frequency Current Probe PT-3510A



Characteristic

- Easy to use and accurate AC/DC current measurements.
- DC-2MHz bandwidth.
- Jaw diameter 20mm.
- High accuracy, 1% DC gain error.
- Split-core structure for easy circuit connection.
- Low noise and DC drift.
- Amplifier not required
- power adapter included.

Model	PT-3510A
Bandwidth(-3dB)	DC-5MHz
AC current	1000Ap-p
Current RMS	350A rms
DC current	500A
Minimum current	20mA
Accuracy	20X:±1%+2mV; 200X:±1%+1mV
Conversion Ratio	50mV/A(20X); 5mV/A(200X)
Measuring range	20X:20mA~50Apeak; 200X:50A~500Apeak
Noise rms	20mA
Rise time	70ns
Coupled mode	AC/DC
Power supply	12V
Clamp Dia	20mm
Operation temp	0~50°C
Operation humidity	20~75%RH
Dimension(L×W×H)	Probe pliers 151.9×64.7×31.8mm
Weight	Approximately 389g

● ACCESSORIES



GUANGZHOU PINTECH CO.,LIMITED

Web:www.pintech.com.cn
 Tel:86-20-82510899
 E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.