

Description


The WPE0521NB is a bi-directional TVS diode, utilizing leading monolithic silicon technology to provide fast response time and low ESD clamping voltage, making this device an ideal solution for protecting voltage sensitive high-speed data lines. The WPE0521NB has an ultra-low capacitance with a typical value at 0.25pF, and complies with the IEC 61000-4-2 (ESD) standard with $\pm 20\text{kV}$ air and $\pm 20\text{kV}$ contact discharge. It is assembled into an ultrasmall 0.6x0.3x0.3mm lead-free DFN package. The small size, ultra-low capacitance and high ESD surge protection make WPE0521NB an ideal choice to protect cell phone, digital video interfaces, HDMI, DVI, USB2.0, USB3.0, and other high speed ports.

Features

- Ultra small package: 0.6x0.3x0.3mm
 - Ultra low capacitance: 0.3pF typical
 - Ultra low leakage: nA level
 - Low operating voltage: 5V
 - Low clamping voltage
 - 2-pin leadless package
 - Complies with following standards:
 - IEC 61000-4-2 (ESD) immunity test
- Air discharge: $\pm 25\text{kV}$
 Contact discharge: $\pm 22\text{kV}$
 – IEC61000-4-5 (Lightning) 4A (8/20 μs)

- RoHS Compliant

Dimensions& Symbol (Unit: mm Max)




Mechanical Characteriisstics

- Package: DFN0603-2L (0.6×0.3×0.3mm)
- Lead Finish: NiPdAu
- Case Material: “Green” Molding Compound.
- UL Flammability Classification Rating94V-0
- Moisture Sensitivity: Level 3 per J-STD-020
- Terminal Connections: See DiagramBelow
- Marking Information: SeeBelow

Applications

- Cellular Handsets and Accessories
- Display Ports
- MDDI Ports
- USB Ports
- Digital Video Interface (DVI)
- PCI Express and Serial SATA Ports

Marking information



Ordering Information

PartNumber	Packaging	ReelSize
WPE0521NB	10000/Tape&Reel	7inch

Absolute maximum ratings($T_A=25^{\circ}\text{C}$, RH=45%-75%, unless otherwise noted)


Parameter	Symbol	Value	Unit
Peak Pulse Power(8/20 μs)	Ppk	100	W
Peak Pulse Current(8/20 μs)	I _{PP}	4	A
ESD per IEC 61000-4-2(Air)	V _{ESD}	±25	kV
ESD per IEC 61000-4-2(Contact)		±22	
Operating TemperatureRange	T _J	-55 to+125	°C
Storage TemperatureRange	T _{stg}	-55 to+150	°C

Electrical characteristics($T_A=25^{\circ}\text{C}$)


Parameter	Symbol	Min	Typ	Max	Unit	TestCondition
Reverse WorkingVoltage	V _{RWM}			5.0	V	
BreakdownVoltage	V _{BR}	6.5		9.5	V	I _T =1mA
Reverse LeakageCurrent	I _R		0.02	0.2	μA	V _{RWM} =5.0V
ClampingVoltage	V _C			12	V	I _{PP} = 1A (8 x 20μspulse)
ClampingVoltage	V _C			25	V	I _{PP} = 4A (8 x 20μspulse)
JunctionCapacitance	C _J		0.3	0.5	pF	V _R = 0V, f =1MHz

WPMtek


Typical Performance Characteristics ($T_A=25^{\circ}\text{C}$ unless otherwise Specified)




Junction Capacitance vs. Reverse Voltage




Peak Pulse Power vs. Pulse Time




Clamping Voltage vs. Peak Pulse Current



Power Derating Curve



8 X 20μs Pulse Waveform




ESD Clamping Voltage


8 kV Contact per IEC61000-4-2

Soldering parameters

Reflow Condition		Pb-Free assembly (see FIG.2)
Pre Heat	-Temperature Min ($T_{s(min)}$)	+150°C
	-Temperature Max($T_{s(max)}$)	+200°C
	-Time (Min to Max) (t_s)	60-180 secs.
Average ramp up rate (Liquid us Temp (T_L) to peak)		3°C/sec. Max
$T_{s(max)}$ to T_L - Ramp-up Rate		3°C/sec. Max
Reflow	-Temperature(T_L) (Liquid us)	+217°C
	-Temperature(t_L)	60-150 secs.
Peak Temp (T_p)		+260(+0/-5)°C
Time within 5°C of actual Peak Temp (t_p)		30 secs. Max
Ramp-down Rate		6°C/sec. Max
Time 25°C to Peak Temp (T_p)		8 min. Max
Do not exceed		+260°C




Package mechanical data



SYM	DIMENSIONS		
	MILLIMETERS		
	MIN	NOM	MAX
A	0.230		0.330
A1	0.000	0.020	0.050
b	0.215	0.245	0.275
c	0.120	0.150	0.180
D	0.550	0.600	0.650
e	0.355BSC		
E	0.250	0.300	0.350
L	0.160	0.190	0.220
h	0.079BSC		

Suggested Land Pattern



SYM	DIMENSIONS	
	MILLIMETERS	INCHES
X	0.30	0.012
Y1	0.25	0.010
Y2	0.15	0.006
Y3	0.40	0.016
Z	0.65	0.026

WPMtek reserves the right to make changes to the product specification and data in this document without notice. WPMtek makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does WPMtek assume any liability arising from the application or use of any products or circuits, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Any enquiry, please write to sales@wpmtek.com for further information.