

Differential Probe DP-50



Characteristic

- 2% accuracy.
- Adaptor power supply.
- Standard BNC interface, compatible with any brand's oscilloscope.

Model	DP-50
Bandwidth(-3dB)	100X:DC-25MHz; 200X:DC-50MHz; 500X:DC-50MHz; 1000X:DC-50MHz
Attenuation Ratio	100X,200X,500X,1000X
Accuracy	±2%
Rise Time	≥7ns
Input differential Vp-p	100X:700V; 200X:1400V; 500X:3500V; 1000X:7000V
Input differential V AC RMS	2300V
Input differential V DC	100X:350V; 200X:700V; 500X:1700V; 1000X:3500V
Common mode voltage(rms)	1200V
Input Impedance	8MΩ//2.4pF(Single-ended); 16MΩ//1.2pF(Both ends)
Noise RMS	≤2mV rms
Oscilloscope input impedance	1MΩ
Power adaptor	9V adapter
CMRR(Typical)	60Hz:>80dB; 100Hz:>60dB; 1MHz:>50dB
Temperature	0~50°C
Humidity	10~85%RH
Weight	280g
Dimension(L*W*H)	240×80×30mm

● ACCESSORIES



9V Adapter



BP-250



BP-266N



BP-276N



BP-366A

GUANGZHOU PINTECH CO.,LTD

Web:www.pintech.com.cn

Tel:020-82510899

E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.