



RoHS

REV.	ECN.#	DESCRIPTION	NAME	DATE
A0		NEW RELEASE	liuhongping	2023.01.02








A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME



NOTES:

- MATERIAL:
  - HOUSING: LCP UL94V-0; COLOR: BLACK
  - TERMINAL: C7025
  - SHELL: SUS304
  - MID PLATE: SUS301
- FINISH:
  - TERMINAL: G/F PLATED ON CONTACT AREA; G/F PLATED ON SOLDER AREA; Ni 30u" MIN. UNDERPLATED OVERALL.
  - SHELL: Ni 30u" MIN. PLATED OVERALL
  - MID PLATE: CLEANING.
- ELECTRICAL SPECIFICATION:
  - RATED CURRENT: VBUS AND GND PIN 5.0A; OTHER PIN 0.25A
  - CONTACT RESISTANCE: 40mΩ MAX(INITIAL). 50mΩ MAX (AFTER).
  - INSULATION RESISTANCE: 100MΩ MIN.
  - DIELECTRIC WITHSTANDING VOLTAGE: 100V AC R.M.S.
- MACHINERY SPECIFICATION:
  - MATING FORCE: 5N~20N. UNMATING FORCE: 8N~20N. (AFTER TEST:6N~20N).
  - DURABILITY: 10000 CYCLES MIN.
- ENVIRONMENTAL SPECIFICATION:
  - OPERATING CONDITION: TEMPERATURE-40°C~+85°C; HUMIDITY 80% R.H MAX
  - SALT SPRAY: 24H
  - SOLDER ABILITY: 245±5°C, 5±0.5s
  - IR REFLOW: THE PEAK TEMPERATURE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 260°C.



RECOMMENDED PCB LAYOUT  
TOLERANCE=±0.05

MILLIMETERS	INCH
X.* ±2*	X.* ±2*
X ±0.30	.X ±0.012
XX ±0.20	.XX ±0.008
XXX ±0.10	.XXX ±0.004


THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd  
COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd



东莞市金比莱五金塑胶科技有限公司  
DONGGUAN JBL TECH CO., LTD

TITLE	TYPE C 16 PIN板上SMT 带定位柱L7.35 无弹片 高导电	DR	
PART NO.	104312272-E	CHKD	
PRO J.	PAGE 1/2 UNITS mm	APPD	
SIZE	A4 SCALE 1:1 DIS NO.		


RoHS




COVER TAPE PEELING ANGLE:  $165^\circ \sim 180^\circ$   
 PEELING FORCE:  $20 \sim 130g$

CARRIER TAPE

USER DIRECTION OF UNREELING




DETAIL B




NOTES

1. NUMBER OF CONNECTORS: 1000PCS/REEL
2. LEAD TAPE LENGTH



3. QUANTITY: 15000PCS/CARTON



MILLIMETERS	INCH	东莞市金比莱五金塑胶科技有限公司 DONGGUAN JBL TECH CO., LTD			
X.* $\pm 2^*$	X.* $\pm 2^*$	TITLE TYPE C 16 PIN板上SMT 带定位柱L7.35 无弹片 高导电		DR	
X $\pm 0.30$	.X $\pm 0.012$	PART NO. 104312272-E		CHKD	
XX $\pm 0.20$	.XX $\pm 0.008$	PRO J.	PAGE 2/2	UNITS mm	APPD
XXX $\pm 0.10$	.XXX $\pm 0.004$	SIZE A4	SCALE 1:1	DIS NO.	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF DongGuan JinBiLai Metal Plastic Technology Co.,Ltd					