

BACK VIEW



MATERIAL:

HOUSING : PBT,UL94V-0,BLACK.

TERMINALS BRACKET: PBT,UL94V-0,BLACK.

SHIELD: C2680,T=0.20MM,NICKEL PLATING ON ALL AREA.

TERMINAL: PHOSPHOR BRONZE C5210,T=0.35MM,

6U" GOLD PLATING ON CONTACT AREA.

MECHANICAL:


DURABILITY : 750 CYCLES MIN.


MATING FORCE : 23N MAX.

OPERATING TEMPERATURE: -40°C~+85°C.


STORAGE TEMPERATURE: -40°C~+85°C.

ALL CRITICAL DIMENSIONS WITH "*"




TOLERANCE:		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME:	
X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X. ±2" X.X ±0.5"				RJ45 90° DIP 带灯带屏蔽1000BASE	
 UNIT: mm [inch]		CHECKED BY:	DATE :	PART NO.	HYCW561-RJ45-211B-911131A
		马跃	2014-02-23	MOLD NO.	
SCALE:1:1 SIZE: A4		APPROVED BY:	DATE :	DRAW NO:	HYC-2504101631
		邱敏	2014-02-23	SHEET NO.	1 OF 1

RECOMMENDED PANEL CUTOUT (REFERENCE ONLY) :



UNIT: MM / INCH
TOLERANCES: ± 0.10 / 0.004
REFERENCE ONLY

KEEP-OUT AREA (COMPONENT SIDE VIEW) :






PLUG-IN SIDE

UNIT: MM / INCH
TOLERANCES: ± 0.10 / 0.004



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X." ± 2 " X.X" ± 0.5 "	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: RJ45 90° DIP 带灯带屏蔽1000BASE
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW561-RJ45-211B-911131A
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.
			DRAW NO: HYC-2504101631
			SHEET NO. 1 OF 1

**Electrical:**

- 1.Turn ratio:1~2:J1~J2=1CT:1CT($\pm 2\%$).
3~4:J3~J6=1CT:1CT($\pm 2\%$).
7~8:J4~J5=1CT:1CT($\pm 2\%$).
9~10:J7~J8=1CT:1CT($\pm 2\%$).
- 2.OCL:350uH Min.at 100KHz 100mV 8mA DC.
- 3.Insertion Loss: -1.0 dB Max 1~100MHz.
- 4.Return loss: -18dB Min 1~30MHz;
-14dB Min 30~60MHz.
-12dB Min 60~80MHz.
-10dB Min 80~100MHz.
- 5.Cross talk: -40dB Min 1~30MHz;
-35dB Min 30~60MHz;
-30dB Min 60~100MHz;
- 6.CMR: -30dB Min 1~100MHz;
- 7.Hi-Pot:2250V DC 6S 1mA PRI TO SEC

LED Specification

Standard LED Color	LED Wavelength	Foward(A)	Foward(V)
Green	568nm	20mA	1.85-2.45V
Yellow	585nm	20mA	1.7-2.2V



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ± 0.30
X.XX ± 0.25
X.XXX ± 0.15
X." ± 2 " X.X" ± 0.5 "



UNIT: mm [inch]

SCALE:1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

RJ45 90° DIP 带灯带屏蔽1000BASE

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW561-RJ45-211B-911131A

MOLD NO.**APPROVED BY:**

邱敏

DATE :

2014-02-23


DRAW NO:

HYC-2504101631

SHEET NO.

1 OF 1

PROFILE OF WAVE SOLDER




A.Preheating B.Soldering C.Gradual Cooling
Tip temperature:260±5°C.
Tip temperature time:5Sec Max.
Tip melting point of Sn96.5/Ag3/Cu0.5:217°C.

Remarks: after wave soldering, the plastic positioning columns of the product which under the PCB will be slightly melted, but it won't affect its function.



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: RJ45 90° DIP 带灯带屏蔽1000BASE	
 UNIT: mm [inch] SCALE:1:1 SIZE: A4		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HVCW561-RJ45-211B-911131A	
		APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2504101631	
				SHEET NO. 1 OF 1	