


Features

- 2-pin lead-less package
- Junction capacitance (Max value: 85pF)
- Peak Pulse Current (8/20 μ s): 35A
- IEC61000-4-2 (ESD) $\pm$ 30kV (air), $\pm$ 30kV (contact)
- Low clamping voltage
- Low leakage current
- Working voltages:12V
- RoHS Compliant

Appearance & Symbol




Mechanical Characteristics

- Package: DFN1006
- Lead Finish:Matte Tin
- Case Material: “Green” Molding Compound.
- UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 3 per J-STD-020
- Tape Reel :10000pcs

Applications

- Cellular Handsets and Accessories
- Personal Digital Assistants
- Notebooks and Handhelds
- Portable Instrumentation
- Digital Cameras,Peripherals
- Audio Players

Marking Information



12S=Marking Code

Absolute Maximum Ratings (T=25°C, RH=45%-75%, unless otherwise noted)

Parameters	Symbol	Value	Unit
Peak Pulse Power (tp=8/20μs waveform)	P _{PP}	1260	W
Peak Pulse Current (8/20μs)	I _{PP}	35	A
Forward Voltage(I _F =10mA)	V _F	1.2	V
ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	V _{ESD}	±30 ±30	KV
Operating Temperature Range	T _J	-55 to +125	°C
Storage Temperature Range	T _{stg}	-55 to +150	°C

Electrical Characteristics (T=25°C, RH=45%-75%, unless otherwise noted)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Reverse Working Voltage	V _{RWM}				12	V
Reverse Breakdown Voltage	V _{BR}	I _R = 1mA	13.3		15	V
Reverse Leakage Current	I _R	V _R = 12V			0.2	uA
Clamping Voltage	V _C	I _{PP} = 1A, T _P =8/20us			16	V
Clamping Voltage	V _C	I _{PP} = 13A, T _P =8/20us			24	V
Clamping Voltage	V _C	I _{PP} = 35A, T _P =8/20us			36	V
Junction Capacitance	C _J	V _R = 0V, f = 1MHz			85	pF

Typical Characteristics

FIG1: Power rating derating curve




FIG2: pulse Waveform




FIG3: Capacitance between terminals characteristics






FIG4: Clamping Voltage vs. Peak Pulse Current




Soldering parameters

Reflow Condition		Pb-Free assembly (see as bellow)
Pre Heat	-Temperature Min ($T_{s(min)}$)	+150°C
	-Temperature Max($T_{s(max)}$)	+200°C
	-Time (Min to Max) (t_s)	60-180 secs.
Average ramp up rate (Liquid us Temp (T_L) to peak)		3°C/sec. Max
$T_{s(max)}$ to T_L - Ramp-up Rate		3°C/sec. Max
Reflow	-Temperature(T_L) (Liquid us)	+217°C
	-Temperature(t_L)	60-150 secs.
Peak Temp (T_p)		+260(+0/-5)°C
Time within 5°C of actual Peak Temp (t_p)		30 secs. Max
Ramp-down Rate		6°C/sec. Max
Time 25°C to Peak Temp (T_p)		8 min. Max
Do not exceed		+260°C




Package mechanical data



Symbol	Dimension in Millimeters	
	min	max
A	0.4	0.5
A1	0	0.05
D	0.9	1.1
E	0.55	0.65
e	(0.65)	
b	0.2	0.3
L	0.34	0.55

Suggested Land Pattern



Symbol	Dimension in Millimeters
	typ
X	(0.5)
Y	(0.7)
P	(0.8)