






P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-15-013750	17SEP2015	DW	CW
	B1	ECR-15-016224	05NOV2015	DW	CW
	C	ECR-20-016101	09JUN2021	BS	CW
	D	ECR-25-246907	18JUN2025	ABS	RB



M4 SCREW
RECOMMENDED
TIGHTENING TORQUE 1.2Nm




4X M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5Nm

NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 250 V
RATED CURRENT: 16 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 4 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.5-2.5 mm² (20-14 AWG)
CONTACT FINISH: SILVER PLATED
CONTACT TYPE: SCREW CONTACT

注释:
1. 技术参数:
绝缘材料: PC
额定电压: 250V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 4 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500 次
接线范围: 0.5-2.5 mm² (18-14 AWG)
端子表面处理: 镀银
接线类型: 螺丝连接


PANEL CUT FOR INSERTS FOR USE
WITHOUT HOODS/ HOUSINGS



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



MATERIAL

-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC $\pm$ -
1 PLC $\pm$ -
2 PLC $\pm$ -
3 PLC $\pm$ -
4 PLC $\pm$ -
ANGLES $\pm$ -

FINISH

-

DWN 10NOV2014

David Wang

CHK 10NOV2014

Chris Wang

APVD 10NOV2014

Xiang Xu

PRODUCT SPEC

108-137045

APPLICATION SPEC

114-137045

WEIGHT

-

CUSTOMER DRAWING

HA-016-F

T2010162201-000

DESCRIPTION

PART NUMBER



TE Connectivity

NAME

HA-016-F

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

©-T2010162201000

-

SCALE

1:1

SHEET

1 OF 1

REV

D