

[Automotive Parts](#) > [Automotive Connector Accessories](#) > [Automotive Connector Caps & Covers](#)Primary Product Color: **Black**Protection & Strain Relief Accessory Type: **Cover - Cable Exit**Primary Product Material: **PA GF**Strain Relief: **Without**Operating Temperature (Max): **65 °C, 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C [ 248 °F ]**

## Features

### Product Type Features

Protection & Strain Relief Accessory Type	Cover - Cable Exit
---	--------------------

### Body Features

Primary Product Color	Black
-----------------------	-------

Primary Product Material	PA GF
--------------------------	-------

### Mechanical Attachment

Strain Relief	Without
---------------	---------

### Usage Conditions

Operating Temperature (Max)	65 °C, 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C [ 248 °F ]
-----------------------------	---

Operating Temperature Range	-40 – 120 °C [-40 – 248 °F]
-----------------------------	-----------------------------

### Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

### Packaging Features

Packaging Method	Box
------------------	-----

### Other

Serviceable

Yes

## Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # CAT-M8793-CH8172  
MQS, CONNECTOR HOUSING

## Customers Also Bought



TE Part #CAT-M8793-T273  
MQS, RECEPTACLE AND TAB



TE Part #1-1355135-1  
RETAINER 94P



TE Part #CAT-M8793-CH8172  
MQS, CONNECTOR HOUSING




TE Part #1-1579018-4  
EXTRACTION TOOL



TE Part #1746817-1  
SEALED EFI ECU 60P PLUG WIRE COVER



TE Part #1747142-1  
SEALED EFI ECU 60POS LEVER R



TE Part #925470-1  
25P MINI TIMER HSG



TE Part #1612283-1  
SEALED 0.64/2.3II 60POS PLUG A

## Documents

### Product Drawings

#### SHIELD, 94POSN., RECEPTACLE HO

English

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-1355132-2\\_A.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-1355132-2\\_A.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1-1355132-2\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

#### Product Specification

German