







说明:

1. 产品表面清洁, 无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
2. 塑胶材料: LCP UL94V-0, 颜色: 本色;
3. 焊片: 黄铜, 镀底30u"Min., 镀锡50u"Min.;
4. 接触针: 黄铜, 镀底30u"Min., 镀锡50u"Min.;
5. 满足灼热丝温度850度.
6. 工作温度: -40~+85°C
7. 额定电流: 0.7A AC/DC
8. 额定电压: 30V AC/DC
9. 接触阻抗: 30mΩ Max.
10. 绝缘阻抗: 100MΩ Min.
11. 耐压: 200V AC FOR 1 MINUTE



P/N	PIN	DIM A	DIM B	DIM C	DIM D
XY-0.8-2PWT	2	0.80	3.04	3.80	1.90
XY-0.8-3PWT	3	1.60	3.84	4.60	2.70
XY-0.8-4PWT	4	2.40	4.64	5.40	3.50
XY-0.8-5PWT	5	3.20	5.44	6.20	4.30
XY-0.8-6PWT	6	4.00	6.24	7.00	5.10
XY-0.8-7PWT	7	4.80	7.04	7.80	5.90
XY-0.8-8PWT	8	5.60	7.84	8.60	6.70
XY-0.8-9PWT	9	6.40	8.64	9.40	7.50
XY-0.8-10PWT	10	7.20	9.44	10.20	8.30
XY-0.8-11PWT	11	8.00	10.24	11.00	9.10
XY-0.8-12PWT	12	8.80	11.04	11.80	9.90
XY-0.8-13PWT	13	9.60	11.84	12.60	10.70
XY-0.8-14PWT	14	10.40	12.64	13.40	11.50
XY-0.8-15PWT	15	11.20	13.44	14.20	12.30
XY-0.8-16PWT	16	12.00	14.24	15.00	13.10
XY-0.8-17PWT	17	12.80	15.04	15.80	13.90
XY-0.8-18PWT	18	13.60	15.84	16.60	14.70
XY-0.8-19PWT	19	14.40	16.64	17.40	15.50
XY-0.8-20PWT	20	15.20	17.44	18.20	16.30



PCB Layout

DIMENSION IN mm

TOLERANCE UNLESS
OTHERWISE SPECIFIED

.X±0.50 X.*± 5°

.XX±0.20 .X.*± 3°

.XXX±0.10 .XX.*± 1°

厦门市辛译精密电子有限公司
Xiamen XinYi Xyconn Electronics Co.,Ltd

APR. Alex

CHK. Jack

DRA. Can

TITLE:
0.8-NP贴片, 卷装, 亮锡, LCP

DWG NO. XY-0.8-NPWT

PROJ.

CUSTOMER DRAWING

SIZE A4

SCALE 1:1

SHEET 1/1

REV. A