





P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	ECR-15-016224	05NOV2015	DW	CW
	B2	ECR-18-008588	09JUL2018	KW	CW
	C	ECR-20-016101	09JUN2021	BS	CW
	D	ECR-25-246907	18JUN2025	ABS	RB


NOTES:
1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 250 V
RATED CURRENT: 16 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 4 kV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.5-2.5 mm² (20-14 AWG)
CONTACT FINISH: SILVER PLATED
CONTACT TYPE: SCREW CONTACT

注释:
1. 技术参数:
绝缘材料: PC
额定电压: 250V
额定电流: 16A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 4 kV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500 次
接线范围: 0.5-2.5 mm² (20-14 AWG)
端子表面处理: 镀银
接线类型: 螺丝连接





4X M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5Nm

M4 SCREW
RECOMMENDED
TIGHTENING TORQUE 1.2Nm



PANEL CUT FOR INSERTS FOR USE
WITHOUT HOODS/ HOUSINGS



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 10NOV2014 David Wang	 TE Connectivity		
		CHK 10NOV2014 Chris Wang			
		APVD 10NOV2014 Xiang Xu			
		PRODUCT SPEC 108-137045			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME HA-016-M		
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	SIZE CAGE CODE DRAWING NO RESTRICTED TO A300779 C-T2010162101000 -		
		FINISH -			
MATERIAL -		WEIGHT -	SCALE 1:1 SHEET 1 OF 1 REV D		
		CUSTOMER DRAWING			