




TE Internal #: 1-1473776-7  
Board-to-Board, 10 Position, 2.5 mm [.098 in] Centerline,  
Receptacle, 30 VDC, Vertical, Printed Circuit Board, Power & Signal,  
DC Jack Connectors

[View on TE.com >](#)

Connectors > PCB Connectors > Battery Connectors & Holders > DC Jack Connectors



Connector System: **Board-to-Board**  
Number of Positions: **10**  
Centerline (Pitch): **2.5 mm [ .098 in ]**  
Connector & Housing Type: **Receptacle**  
Operating Voltage: **30 VDC**

Features

Product Type Features

Connector System	Board-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	10
PCB Mount Orientation	Vertical

Electrical Characteristics

Operating Voltage	30 VDC
-------------------	--------

Contact Features

Contact Current Rating (Max)	6 A
------------------------------	-----

Mechanical Attachment

PCB Mount Retention	With
PCB Mount Retention Type	Locating Post
Connector Mounting Type	Board Mount



Housing Features

Centerline (Pitch)	2.5 mm[.098 in]
--------------------	-----------------

Usage Conditions

Operating Temperature Range	-20 – 80 °C[-4 – 176 °F]
-----------------------------	--------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Method	Tray
Packaging Quantity	100

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 1674231-1  
2.5MM PITCH HIGH CURRENT BATTE



TE Part # 1123684-7  
2.5 BATTERY CONN PLUG 10P STD

Customers Also Bought



TE Part #ANT-GNCP-CA158L160  
Antenna GNSS L1 15x15 LNA 1.13 UFL



TE Part #CAT-H857-H34225  
AMP HPI 2.5 mm Headers



TE Part #440133-6  
2.5MM,HSG,6POS



TE Part #440134-1  
2.5mm,Crimp Contact



TE Part #1622960-1  
CRG0603 1% 4K7



TE Part #1-2176339-5  
CRGCQ 0603 150R 1%

Documents

Product Drawings

2.5MM PITCH BATTERY REC ASSEMBLY SMT TYP

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-1473776-7\_F1.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-1473776-7\_F1.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-1473776-7\_F1.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

1-1473776-7

Board-to-Board, 10 Position, 2.5 mm [.098 in] Centerline, Receptacle, 30 VDC, Vertical, Printed Circuit Board, Power & Signal, DC Jack Connectors



Product Specifications

Application Specification

English