



Part Number : [1202530614](#)

Product Description : Contrinex Inductive Sensor, M5 Fully Stainless Steel, 3mm Operating Distance, Non-embeddable, NPN, NC, 0.2m 3-wire PUR Cable, 3-pin M8 Connector, 30mm Housing Length



Series Number : 120253

Status : Not Recommended For New Design

Product Category : Inductive and Photoelectric Sensors

Engineering Number : DW-AV-712-M5-276

Documents & Resources

Specifications

[1202530609-000.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | ⓘ per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2025)4165-DC (25 June 2025) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

| | |
|--------------|---|
| Status | Not Recommended For New Design |
| Category | Inductive Sensors |
| Series | 120253 |
| Description | Contrinex Inductive Sensor, M5 Fully Stainless Steel, 3mm Operating Distance, Non-embeddable, NPN, NC, 0.2m 3-wire PUR Cable, 3-pin M8 Connector, 30mm Housing Length |
| IP Rating | IP68, IP69K |
| Product Name | Contrinex |
| Type | Inductive |
| UPC | 191130064601 |

Electrical

| | |
|---------------------|-----------|
| Output | NC |
| Polarity | NPN |
| Switching Frequency | ≤ 1200 Hz |

Physical

| | |
|-------------------------|---|
| Connection | Cable (PUR 0.2m, 3-wire), Connector (M8, 3-pin) |
| Length | 30mm |
| Material - Housing | Stainless Steel |
| Material - Sensing Face | Stainless Steel |
| Mounting Style | Non-embeddable |

| | |
|-------------------------------|---------------|
| Operating Distance | 3mm |
| Output | NC |
| Sensor Housing Size | M5 |
| Temperature Range - Operating | -25° to +85°C |

This document was generated on Nov 07, 2025