




EMI & EMC Solutions > IEC Inlets > Power Entry Modules > High Performance Filters, Corcom P Series



Filter Type: **Power Entry Module**
Input Voltage Selection: **Single AC**
Filter Switch Type: **DPST**
Filter Shield Type: **Complete Can**
Product Orientation: **Vertical**

[All High Performance Filters, Corcom P Series \(20\)](#)

Features

Product Type Features

Ground Choke Option	No
Filter Type	Power Entry Module
Filter Switch Type	DPST
Output Termination Type	.250" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 320/C-14

Configuration Features

Extender Options	None
Fuse Options	Single

Electrical Characteristics

Input Voltage Selection	Single AC
Leakage Current (Max) (120VAC, 60Hz)	250 μ A



Leakage Current (Max) (250VAC, 50Hz)	500 μ A
Current Rating	10 A
Operating Voltage	250 VAC

Body Features

Filter Shield Type	Complete Can
Product Orientation	Vertical

Mechanical Attachment

Panel Mount Feature Type	Flange
--------------------------	--------

Dimensions

Panel Thickness (Recommended)	.13 – 1 mm
-------------------------------	------------

Usage Conditions

Operating Temperature Range	-10 – 40 °C[14 – 104 °F]
-----------------------------	--------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts




TE Part # 1609140-1
PA100=F6800



TE Part # 1609146-2
PA102 CONNECTOR PIN=F6999



TE Part # 1609146-1
PA101 CONNECTOR PLU=F6998




TE Part # 1609140-3
PA105 J0=F6806

Also in the Series | Corcom P



EMI & EMC Accessories(4)



Medical Power Entry Modules(1)



Power Entry Modules(367)

Customers Also Bought



TE Part #1-66400-0
III+ PIN,24-20,TIN,LP



TE Part #3-640601-2
02P MTA156 CONN ASSY 22AWG LF



TE Part #3-641438-3
03P MTA156 PSTD CONN ASSY WHT



TE Part #3-644466-4
04P MTA156 CONN ASSY 20AWG YEL



TE Part #1-794609-2
PIN CONT 26-30 30 GOLD STRIP




TE Part #1614884-9
CPF 0805 4R7 0.1% 25PPM 1K RL




TE Part #1734320-1
RJ45, W/ PANEL, Y/G LEDS, DIP, 6U"
Au



TE Part #2-1879075-8
THS25 22R 5%



TE Part #2-1879642-5
[H8 2K5 0.1% 50PPM](#)



TE Part #7-2176238-0
[CPF A 0805 1M0 0.1% 25PPM 5K RL](#)

Documents

Product Drawings

[PE0S0SZXC M0=C7046](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_6609108-6_B1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6609108-6_B1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6609108-6_B1.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Corcom Combined Selector Charts](#)

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English

[1654001_CORCOM_PRODUCT_GUIDE_P_SERIES](#)

English