

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	25FEB2015	GY	CW
	B	ECR-15-017607	03DEC2015	GY	CW
	C	ECR-21-117384	05NOV2021	W QR	CW
	D	ECR-25-237617	12MAR2025	ABS	RB

NOTES:

- I. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC(Gray)
RATED VOLTAGE: CONDUCTOR-GROUND: 400V
CONDUCTOR-CONDUCTOR: 690V
RATED CURRENT: 35A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
CONTACT RESISTANCE: $\leq 5m\Omega$
FLAMMABILITY: UL94V-0
MATING CYCLES: 500
OPERATION TEMPERATURE: $-40^{\circ}C \sim +125^{\circ}C$
WIRE RANGE: 1.5mm²~6.0mm² (AWG16-AWG10)
CONTACT FINISH: SILVER PLATED
CONTACT TYPE: SCREW CLAMP (M4)

注释:

- I. 技术参数:
绝缘材料: PC(Gray)
额定电压: 导体-地: 400V
导体-导体: 690V
额定电流: 35A
绝缘电阻: $\geq 400M\Omega$
脉冲电压: 6KV
污染等级: 3
接触电阻: $\leq 5 m\Omega$
阻燃等级: UL94V-0
插拔次数: 500
工作温度: $-40^{\circ}C \sim +125^{\circ}C$
接线范围: 1.5mm²~6.0mm² (AWG16-AWG10)
端子表面处理: 镀银
接线类型: 螺丝压接 (M4)

HSB-006-M	T2060062101-000
DESCRIPTION	PART NUMBER



NAME		HSB-006-M			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
A3	-	©T2060062101000	-		
SCALE		SHEET	OF	REV	
1:1		1	1	D	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	10Dec2014
		Gino.Yao	
		CHK	10Dec2014
		Chris.Wang	
		APVD	10Dec2014
		Xiang.Xu	
PRODUCT SPEC		108-137052	
APPLICATION SPEC		114-137052	
WEIGHT		-	
CUSTOMER DRAWING			
DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:		
mm			
	0 PLC	±	
	1 PLC	±	
	2 PLC	±	
	3 PLC	±	
	4 PLC	±	
ANGLES		±	
FINISH			
-		-	
-		-	

M4 thread, recommended tightening torque 1.2Nm
6 X M4 thread, recommended tightening torque 1.2Nm

4 X M3 thread, recommended tightening torque 0.5Nm

