


Item (Detail view)

2-conductor through terminal block; 4 mm²; lateral marker slots; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®

Note: Some items may not be available from your local WAGO company.
Please note that the quantities ordered in the shopping cart are rounded up to the PU (SPU)

RoHS ✓
Compliant



Description	2-conductor through terminal block; 4 mm², lateral marker slots; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®																																																																																
Remarks																																																																																	
Item properties	<table><tr><th colspan="3">Miscellaneous</th></tr><tr><th>Name</th><th>Value</th><th>Unit</th></tr><tr><td>Connection technology</td><td>CAGE CLAMP®</td><td></td></tr><tr><td>Actuation type</td><td>Operating tool</td><td></td></tr><tr><td>Connectable conductor materials</td><td>Copper</td><td></td></tr><tr><td>Solid conductor</td><td>0.08 ... 4 mm² / 28 ... 12 AWG</td><td></td></tr><tr><td>Fine-stranded conductor</td><td>0.08 ... 4 mm² / 28 ... 12 AWG</td><td></td></tr><tr><td>Strip length</td><td>9 ... 10 mm / 0.35 ... 0.39 inch</td><td></td></tr><tr><td>Total number of connection points</td><td>2</td><td></td></tr><tr><td>Total number of potentials</td><td>1</td><td></td></tr><tr><td>Number of levels</td><td>1</td><td></td></tr><tr><td>Type of wiring</td><td>Front-entry wiring</td><td></td></tr><tr><td>Width</td><td>6 mm / 0.236 in</td><td></td></tr><tr><td>Height from upper-edge of DIN-35 rail</td><td>29 mm / 1.142 in</td><td></td></tr><tr><td>Depth</td><td>53 mm / 2.087 in</td><td></td></tr><tr><td>Design</td><td>horizontal</td><td></td></tr><tr><td>Type of mounting</td><td>Carrier rail 35 x 15</td><td></td></tr><tr><td>Marking level</td><td>Slide marking</td><td></td></tr><tr><td>Color</td><td>gray</td><td></td></tr><tr><td>Insulating material</td><td>Polyamide 66 (PA 66)</td><td></td></tr><tr><td>Fire load [MJ]</td><td>0.128</td><td>MJ</td></tr><tr><td>Weight [g]</td><td>7.03</td><td>g</td></tr><tr><td>Packaging type</td><td>BOX</td><td></td></tr><tr><td>[mm]</td><td>6</td><td>mm</td></tr><tr><td>Main product function</td><td>Through term. block</td><td></td></tr><tr><td>Product type</td><td>Through rail-mount term. blocks</td><td></td></tr></table>			Miscellaneous			Name	Value	Unit	Connection technology	CAGE CLAMP®		Actuation type	Operating tool		Connectable conductor materials	Copper		Solid conductor	0.08 ... 4 mm² / 28 ... 12 AWG		Fine-stranded conductor	0.08 ... 4 mm² / 28 ... 12 AWG		Strip length	9 ... 10 mm / 0.35 ... 0.39 inch		Total number of connection points	2		Total number of potentials	1		Number of levels	1		Type of wiring	Front-entry wiring		Width	6 mm / 0.236 in		Height from upper-edge of DIN-35 rail	29 mm / 1.142 in		Depth	53 mm / 2.087 in		Design	horizontal		Type of mounting	Carrier rail 35 x 15		Marking level	Slide marking		Color	gray		Insulating material	Polyamide 66 (PA 66)		Fire load [MJ]	0.128	MJ	Weight [g]	7.03	g	Packaging type	BOX		[mm]	6	mm	Main product function	Through term. block		Product type	Through rail-mount term. blocks	
Miscellaneous																																																																																	
Name	Value	Unit																																																																															
Connection technology	CAGE CLAMP®																																																																																
Actuation type	Operating tool																																																																																
Connectable conductor materials	Copper																																																																																
Solid conductor	0.08 ... 4 mm² / 28 ... 12 AWG																																																																																
Fine-stranded conductor	0.08 ... 4 mm² / 28 ... 12 AWG																																																																																
Strip length	9 ... 10 mm / 0.35 ... 0.39 inch																																																																																
Total number of connection points	2																																																																																
Total number of potentials	1																																																																																
Number of levels	1																																																																																
Type of wiring	Front-entry wiring																																																																																
Width	6 mm / 0.236 in																																																																																
Height from upper-edge of DIN-35 rail	29 mm / 1.142 in																																																																																
Depth	53 mm / 2.087 in																																																																																
Design	horizontal																																																																																
Type of mounting	Carrier rail 35 x 15																																																																																
Marking level	Slide marking																																																																																
Color	gray																																																																																
Insulating material	Polyamide 66 (PA 66)																																																																																
Fire load [MJ]	0.128	MJ																																																																															
Weight [g]	7.03	g																																																																															
Packaging type	BOX																																																																																
[mm]	6	mm																																																																															
Main product function	Through term. block																																																																																
Product type	Through rail-mount term. blocks																																																																																