



REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A			2024.9.06	
A2	N/A	(A)X1		2025.08.19	



■SPECIFICATIONS





- Voltage rating:250V AC/DC
- Current rating:2.5A AC/DC
- Withstanding Voltage:500V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance:≥ 1000MQ
- Contact resistance:≤20mΩ

PART NO.:

X1511 W V S-XX L HF-LP SW

Series No
Category:W-Wafer
Welding Board Angle:V-Stright 180°
Welding Way:S-SMT
Row No.Pin No:XX-02~15Pin
Special No:L-With lock
Special No:HF-Halogen free
Material:9T-PA9T;46-PA46;LP-LCP 94V-0
Planting:SW-Matte Tin Plating

Poles	Dimensions(mm)		
	A	B	C
02	1.50	4.30	3.70
03	3.00	5.80	5.20
04	4.50	7.30	6.70
05	6.00	8.80	8.20
06	7.50	10.30	9.70
07	9.00	11.80	11.20
08	10.50	13.30	12.70
09	12.00	14.80	14.20
10	13.50	16.30	15.70
11	15.00	17.80	17.20
12	16.50	19.30	18.70
13	18.00	20.80	20.20
14	19.50	22.30	21.70
15	21.00	23.80	23.20



X1511WVS-XXLHF-LPSW	LCP UL 94V-0 Halogen Free	Brass	Matte Tin Plating	X1511H
PART NO	Material	Material(Pin& SolderTab)	Finish(Pin)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN
CHECKED
APPROVED

VIEW:
UNIT: mm/in
SIZE: A4

MODEL TYPE:
1.50mm Crimp Style Connectors
PART NO.:
X1511WVS-XXLHF-LPSW
DWG NO.:

SCALE	PAGE	REVISION
N/A	1/1	A2