



Part Number : [1202530214](#)

Product Description : Contrinex Inductive Sensor, M8 Housing, 2.5mm Operating Distance, Non-embeddable, NPN, NO, 3-pin M8 Connector, 45mm Housing Length



Series Number : 120253

Status : Not Recommended For New Design

Product Category : Inductive and Photoelectric Sensors

Engineering Number : DW-AS-611-M8-001

Documents & Resources

Specifications

[1202530210-000.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | ⓘ per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2025)4165-DC (25 June 2025) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

| | |
|--------------|--|
| Status | Not Recommended For New Design |
| Category | Inductive Sensors |
| Series | 120253 |
| Description | Contrinex Inductive Sensor, M8 Housing, 2.5mm Operating Distance, Non-embeddable, NPN, NO, 3-pin M8 Connector, 45mm Housing Length |
| IP Rating | IP67 |
| Product Name | Contrinex |
| Type | Inductive |
| UPC | 191130063840 |

Electrical

| | |
|---------------------|-----------|
| Output | NO |
| Polarity | NPN |
| Switching Frequency | ≤ 4500 Hz |

Physical

| | |
|-------------------------|-----------------------|
| Connection | Connector (M8, 3-pin) |
| Length | 45mm |
| Material - Housing | Stainless Steel |
| Material - Sensing Face | PBTP |
| Mounting Style | Non-embeddable |
| Operating Distance | 2.5mm |
| Output | NO |

| | |
|-------------------------------|---------------|
| Sensor Housing Size | M8 |
| Temperature Range - Operating | -25° to +70°C |

This document was generated on Nov 07, 2025