



Part Number : [1202530119](#)
Product Description : Contrinex Inductive Sensor,
M18 Housing, 20mm Operating Distance, Non-embeddable, PNP, NC, 2m 3-wire PVC Cable, 36mm Housing Length
Series Number : 120253
Status : Not Recommended For New Design
Product Category : Inductive and Photoelectric Sensors
Engineering Number : DW-AD-514-M18-120




Documents & Resources

Specifications

[1202530116-000.pdf](#)

Product Environment Compliance

Compliance

| | |
|--------------------|--|
| GADSL/IMDS | Not Relevant |
| China RoHS |  per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2024)7663-DC (21 Jan 2025) |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

| | |
|--------------|---|
| Status | Not Recommended For New Design |
| Category | Inductive Sensors |
| Series | 120253 |
| Description | Contrinex Inductive Sensor, M18 Housing, 20mm Operating Distance, Non-embeddable, PNP, NC, 2m 3-wire PVC Cable, 36mm Housing Length |
| IP Rating | IP67 |
| Product Name | Contrinex |
| Type | Inductive |
| UPC | 191130062898 |

Electrical

| | |
|---------------------|----------|
| Output | NC |
| Polarity | PNP |
| Switching Frequency | ≤ 500 Hz |

Physical

| | |
|-------------------------|------------------------|
| Connection | Cable (PVC 2m, 3-wire) |
| Length | 36mm |
| Material - Housing | Chrome Plated Brass |
| Material - Sensing Face | PBTP |
| Mounting Style | Non-embeddable |
| Operating Distance | 20mm |

| | |
|-------------------------------|---------------|
| Output | NC |
| Sensor Housing Size | M18 |
| Temperature Range - Operating | -25° to +70°C |