




| CHARACTERISTICS | | RATING | OPERATING LIFE |
|-------------------------------|-------------|-----------------------|----------------|
| OPERATING FORCE (OF) : | 130gf Max. | 2A 12VDC | 100,000 CYCLES |
| RELEASE FORCE (RF) : | 13gf Min. | 0.1A 48VDC 125/250VAC | 100,000 CYCLES |
| OPERATING POSITION (OP) : | 3.05±0.2mm. | MECHANICAL LIFE | 500,000 CYCLES |
| TOTAL TRAVEL POSITION (TPP) : | 2.05mm Max. | GAP TYPE | MICRO |
| FREE POSITION (FP) : | 3.65mm Max. | OPERATING TEMP | -40°C ~ +85°C |
| | | WATERPROOF | IP67 |



| OUTLINE DRAWING | | | | TOLERANCE UNLESS OTHERWISE SPECIFIED | | | | | | |
|-----------------|------------------------|------|------------|--------------------------------------|--|------|-------|-------------|---------|-------|
| TITLE | H3 SERIES MICRO SWITCH | | | ≤3 | 1~3 | 3~10 | 10~30 | 30~100 | 100~200 | ANGLE |
| MODEL | H3-A | | | ±0.2 | ±0.3 | ±0.4 | ±0.6 | ±1.0 | ±1.5 | ±3.0° |
| PART NO | | | | |  | | | SCALE | | |
| DRAFTED BY | 李春风 | DATE | 2025-05-08 | | UNIT | | | mm | | |
| CHECKED BY | 钟华华 | DATE | 2025-05-08 | | VERSION REV | | | A1 | | |
| APPROVED BY | 罗孝金 | DATE | 2025-05-08 | |  首韩 SHOUHAN | | | 深圳市首韩科技有限公司 | | |



深圳市首韩科技有限公司
SHENZHEN SHOUHAN TECHNOLOGY CO., LTD
Tel: 0755-27597601 Fax: 0755-27597491

承 认 书

SPECIFICATION FOR APPROVAL

产品编码

Material code:

产品名称 Project:

微动开关

规格型号 Part No:

H3-A

贵公司承认印 Approval signatures

| 料号/Part No. | 签章/Signatures |
|-------------|---------------|
| | |

日期 Date:

| | | |
|-------------|-----|--|
| 拟制/Drawn | 李春风 |  |
| 审核/Check | 钟华华 | |
| 批准/Approved | 罗孝金 | |



规 格 书 SPECIFICATION

1. 一般特性 General Characteristics

1.1 额定值(Rating Value): AC 12V 3A

1.2 工作温度(Work Temperature Range): -40°C ~ 85°C

1.3 存贮温度(Store Temperature Range): -20°C ~ 80°C

1.4 正常测试条件(未有特殊说明量测在以下条件进行):

General test condition (Tests and measurements shall be made under the following standard conditions unless otherwise specified):

正常温度: 5°C~35°C 相对湿度: 45%~85% RH 气压: 8,600~10,600 帕

Temperature: 5°C~35°C Relative humidity: 45%~85% Air pressure: 8,600~10,600 pa

2. 产品外观及尺寸要求 Appearance & Dimension Requirement

2.1 产品外形结构紧凑, 无配合不良.

The structure of product is compact, and assembly of parts has no badness.

2.2 产品塑胶部件无严重缩水、披锋、欠注、斑点、破损或变形现象.

The plastic parts of product have no serious defects such as very serious shrink, scarcity, fleck, disrepair, transmutation, etc.

2.3 产品引脚和外壳无严重氧化、脏污、变形、毛刺或电镀不良.

Lead feet and shell have no serious defects such as oxidation, smudge, disrepair, burr, defects on plating.

2.4 开关操作顺畅, 节奏感强, 无明显卡塞现象。

Operating switch is unhindered, rhythmed, and there is not palpable clag.

2.5 产品结构及尺寸参见产品规格图纸。

Construction and dimensions: Refer to individual product drawing.

3. 电气特性 Electronic Characteristics

| No. | 项目 Item | 测试方法 Test Method | 测试设备 Equipment | 特性要求 Requirements |
|-----|--|---|---|---|
| 3.1 | 接触电阻 Contact Resistance | 在低电流 (≤100mA) 条件下测试. Measured at low current (100mA or less). | 低电阻测试仪 Low Resistance Meter | 500mΩ |
| 3.2 | 绝缘阻抗 Insulation Resistance | 测试相邻引脚之间, 引脚与外壳之间的绝缘阻抗. Measurement shall be made between adjacent terminals, between terminal and shell. | 绝缘测试机 Insulation Resistance Tester | 100MΩ |
| 3.3 | 耐压测试 Dielectric Withstand Voltage | 输入一定电压(50~60Hz, 电压值 AC 1000V)1分钟, 漏电流为 2mA, 测试邻近端子间. Apply certain voltage (50~60Hz, AC 1000V) for 1 minute between adjacent contacts of the connector with 2mA leakage sensitivity. | 耐压测试机 Puncture Tester | 没有绝缘破坏. 电弧等异常. No arcing, break down and damaging insulation. |



4. 机械特性 Mechanical Characteristics

| No. | 项目 Item | 测试方法 Test Method | 测试设备 Equipment | 特性要求 Requirements |
|-----|------------------------|---|--------------------|----------------------|
| 4.1 | 操作力 Operation Force | 逐渐施力操作开关按键，测量开关到达全部工作行程时所需的最大操作力度。 Operate the keystoke of the switch and then increase press strength gradually, Measured maximum operation force while the travel of the switch is full. | 测力计 Force Gauge | 100±30gf |

5. 可靠性测试 Reliability trial

| No. | 项目 Item | 测试方法 Test Method | 测试设备 Equipment | 特性要求 Requirements |
|-----|--------------------------------------|--|----------------------|--|
| 5.1 | 可焊性试验 Solder ability Test | 端子顶部被浸入焊锡炉中，温度为 $260\pm 5^{\circ}\text{C}$ ，时间 5 ± 1 秒。 The top of the terminals shall be dipped in the solder bath at $260\pm 5^{\circ}\text{C}$ for 5 ± 1 seconds. | 控温锡炉 Solder Stove | 引脚至少 95% 上锡。 Ninety-five percent of terminals shall be dipped. |
| 5.2 | 寿命试验 Operation Life | 开关在寿命试验设备上以约 60 次 / 分的速度连续被操作，具体次数见规格图示。 Switch shall be operated continuously at about 60 cycles /min without load. | 寿命试验机 Life Tester | 寿命：50000 次 实验后： 绝缘电阻： $10\text{M}\Omega$ Min 操作力：变化在 $\pm 50\%$ 内开关外观及结构无损坏。 Life test: 50000 cycles After test, Insulation resistance: $10\text{M}\Omega$ Min Operating force: Change should be within $\pm 50\%$ of specified value. No abnormalities shall be recognized in appearance and construction. |
| 5.3 | 耐焊接热 Resistance to Soldering heat | 端子焊接部分浸入焊炉，焊炉温度 $250\pm 5^{\circ}\text{C}$ ，焊接时间 5 ± 1 秒。（焊接时不可于端子施加外力）。 Terminals shall be dipped in the solder bath at $250\pm 5^{\circ}\text{C}$ for 5 ± 1 seconds without additional force for terminals. | 控温锡炉 Solder Stove | 本体无变形，能满足于机械、电气性能。 Appearance should be not damaged, electrical and mechanical characteristics shall be satisfied. |



5. 可靠性测试 Reliability trial

| No. | 项 目 Item | 测 试 方 法 Test Method | 测 试 设 备 Equipment | 特 性 要 求 Requirements |
|------|--------------------------------------|--|--|--|
| 5. 4 | 耐高温测试 Resistance to Heat Test | 放置在温度 $80 \pm 2^\circ\text{C}$ 环境中 96 小时后, 再置于正常条件下 1 小时后测定。 The switch shall be stored at a temperature of $80 \pm 2^\circ\text{C}$ for 96 hours, Measurements shall be made after it be subjected to the standard conditions for 1 hour. | 高低温试验机 High & Low Temperature Tester | 外观, 机械及电气性能均符合要求。 Appearance, electrical and mechanical characteristics shall be satisfied. |
| 5. 5 | 耐低温测试 Resistance to Cold Test | 放置在温度 $-20 \pm 2^\circ\text{C}$ 环境中 96 小时后, 再置于正常条件下 1 小时后测定。 The switch shall be stored at a temperature of $-20 \pm 2^\circ\text{C}$ for 96 hours, Measurements shall be made after it be subjected to the standard conditions for 1 hour. | 高低温试验机 High & Low Temperature Tester | 外观, 机械及电气性能均符合要求。 Appearance, electrical and mechanical characteristics shall be satisfied. |
| 5. 6 | 耐湿性测试 Resistance to Humidity Test | 放置于温度 $40 \pm 2^\circ\text{C}$, 相对湿度为 90~96% 环境中 96 小时后, 再置于正常条件下 1 小时后测定(注意要擦去水滴)。 The switch shall be stored at a temperature of $40 \pm 2^\circ\text{C}$, relative humidity 90~96% for 96 hours, Measurements shall be made after it be subjected to the standard conditions for 1 hour (Wipe out water drip). | 恒温恒湿箱 Temperature & Humidity Tester Chamber | 外观, 机械及电气性能均符合要求。 Appearance, electrical and mechanical characteristics shall be satisfied. |
| 5. 7 | 盐雾实验 Salt Mist Test | 试件在下述实验后测量: 1. 温度: $35 \pm 5^\circ\text{C}$ 2. 盐溶液浓度: $5 \pm 1\%$ (质量百分比), 3. 试验时间: 24 小时, 4. 试验后, 将盐沉积物用水冲掉。 The switch shall be checked after following test: 1. Temperature: $35 \pm 5^\circ\text{C}$ 2. Salt solution: $5 \pm 1\%$ (Solids by mass) 3. Duration: 24 hours, 4. After immersing, salt deposit shall be removed by running water. | 盐雾试验机 Salt Spray Tester | 在金属件上没有严重腐蚀斑点。 No remarkable corrosion shall be recognized in metal parts. |