



**Part Number :** [1202530189](#)

**Product Description :** Contrinex Inductive Sensor, 6.5mm Diameter Smooth Housing, 1.5mm Operating Distance, Embeddable, PNP, NC, 2m 3-wire PVC Cable, 35mm Housing Length



**Series Number :** 120253

**Status :** Not Recommended For New Design

**Product Category :** Inductive and Photoelectric Sensors

**Engineering Number :** DW-AD-604-065

## Documents & Resources

### Specifications

[1202530186-000.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	ⓘ per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

### UKCA - Declaration of Conformity

### CE - Declaration of Conformity

## Part Details

### General

Status	Not Recommended For New Design
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, 6.5mm Diameter Smooth Housing, 1.5mm Operating Distance, Embeddable, PNP, NC, 2m 3-wire PVC Cable, 35mm Housing Length
IP Rating	IP67
Product Name	Contrinex
Type	Inductive
UPC	191130063598

### Electrical

Output	NC
Polarity	PNP
Switching Frequency	≤ 5000 Hz

### Physical

Connection	Cable (PVC 2m, 3-wire)
Length	35mm
Material - Housing	Stainless Steel
Material - Sensing Face	PA66
Mounting Style	Embeddable
Operating Distance	1.5mm

Output	NC
Sensor Housing Size	6.5mm dia. (smooth)
Temperature Range - Operating	-25° to +70°C

---

This document was generated on Nov 07, 2025