



Part Number : [1202530361](#)

Product Description : Contrinex Inductive Sensor, M8 Housing, 2mm Operating Distance, Embeddable, PNP, NC, 3-pin M8 Connector, 45mm Housing Length



Series Number : 120253

Status : Not Recommended For New Design

Product Category : Inductive and Photoelectric Sensors

Engineering Number : DW-AS-624-M8-001

Documents & Resources

Specifications

[1202530354-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	ⓘ per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Not Recommended For New Design
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, M8 Housing, 2mm Operating Distance, Embeddable, PNP, NC, 3-pin M8 Connector, 45mm Housing Length
IP Rating	IP67
Product Name	Contrinex
Type	Inductive
UPC	191130065868

Electrical

Output	NC
Polarity	PNP
Switching Frequency	≤ 5000 Hz

Physical

Connection	Connector (M8, 3-pin)
Length	45mm
Material - Housing	Stainless Steel
Material - Sensing Face	PA12
Mounting Style	Embeddable
Operating Distance	2mm
Output	NC
Sensor Housing Size	M8
Temperature Range - Operating	-25° to +70°C

This document was generated on Nov 07, 2025