

### Features

- Output Current of 1A Maximum
- Three-Terminal Adjustable or Fixed Outputs
- Maximum Input Voltage: 18V
- Fast Transient Response
- Current Limit, Safe Operating and Thermal Shutdown Protection
- Line Regulation: 0.2%
- Load Regulation: 0.4%
- Environment Temperature: -50°C~+140°C
- Available in SOT223-3

### Application

- High Efficiency Linear Regulators
- Post Regulator for Switching DC/DC Converter
- Power Management for M/B and Graphic Card
- 2.85V Model for SCSI-2 Active Termination
- Battery Charger
- LCD Monitor and LCD TV
- DVD Decode Board
- ADSL Modem


### Ordering Information

#### LM1117MPX-5.0-TP

SOT223-3 Package

Output voltage: 1.8=1.8V  
2.5=2.5V  
3.3=3.3V  
5.0=5.0V  
ADJ=fixed output

### Package and Pin Configuration



### Absolute Maximum Ratings


|                                          |                  |
|------------------------------------------|------------------|
| Maximum Input Voltage                    | 18V              |
| Operating Junction Temperature ( $T_J$ ) | 150 °C           |
| Environment Temperature ( $T_A$ )        | 140 °C           |
| Storage Temperature Range ( $T_s$ )      | -65 °C to 150 °C |
| Lead Temperature (soldering, 10 seconds) | 260 °C           |

### Electrical Characteristics

$V_{IN} = V_{OUT} + 2V$ ,  $I_O = 10mA$ , and  $T_J = 25$  °C, unless otherwise specified.

| Symbol                        | Parameter         | Test Conditions                                                        | Min   | Typ   | Max   | Unit |
|-------------------------------|-------------------|------------------------------------------------------------------------|-------|-------|-------|------|
| $V_{REF}$                     | Reference Voltage | $I_{OUT} = 10mA$ , $V_{IN} - V_{OUT} = 2V$                             | 1.238 | 1.250 | 1.262 | V    |
|                               |                   | $10mA \leq I_{OUT} \leq 1A$ ,<br>$1.5V \leq V_{IN} - V_{OUT} \leq 12V$ | 1.225 | 1.250 | 1.275 |      |
| $V_{OUT}$                     | Output Voltage    | 1.8V<br>$I_{OUT} = 10mA$ , $V_{IN} = 3.8V$ , $T_J = 25^\circ C$        | 1.782 | 1.80  | 1.818 | V    |
|                               |                   | $0 \leq I_{OUT} \leq 1A$ , $3.2V \leq V_{IN} \leq 12V$                 | 1.764 | 1.80  | 1.836 |      |
|                               |                   | 2.5V<br>$I_{OUT} = 10mA$ , $V_{IN} = 4.5V$ , $T_J = 25^\circ C$        | 2.475 | 2.50  | 2.525 |      |
|                               |                   | $0 \leq I_{OUT} \leq 1A$ , $3.9V \leq V_{IN} \leq 12V$                 | 2.450 | 2.50  | 2.550 |      |
|                               |                   | 3.3V<br>$I_{OUT} = 10mA$ , $V_{IN} = 5V$ , $T_J = 25^\circ C$          | 3.267 | 3.30  | 3.333 |      |
|                               |                   | $0 \leq I_{OUT} \leq 1A$ , $4.75V \leq V_{IN} \leq 12V$                | 3.234 | 3.30  | 3.366 |      |
| $\Delta V_{OUT}$              | Line Regulation   | 5.0V<br>$I_{OUT} = 10mA$ , $V_{IN} = 7V$ , $T_J = 25^\circ C$          | 4.95  | 5.00  | 5.05  | V    |
|                               |                   | $0 \leq I_{OUT} \leq 1A$ , $6.5V \leq V_{IN} \leq 12V$                 | 4.90  | 5.00  | 5.10  |      |
| $\Delta V_{OUT}$              | Line Regulation   | ADJ<br>$I_{OUT} = 10mA$ ,<br>$1.5V \leq V_{IN} - V_{OUT} \leq 13.775V$ |       | 0.035 | 0.2   | %    |
|                               |                   | Fixed<br>$I_{OUT} = 10mA$ , $V_{OUT} + 1.5V \leq V_{IN} \leq 15V$      |       | 9     | 12    | mV   |
| $\Delta V_{OUT}$              | Load Regulation   | ADJ<br>$V_{IN} - V_{OUT} = 3V$ , $10mA \leq I_{OUT} \leq 1A$           |       | 0.2   | 0.4   | %    |
|                               |                   | Fixed<br>$V_{IN} = V_{OUT} + 1.5V$ , $10mA \leq I_{OUT} \leq 1A$       |       | 3     | 10    | mV   |
| $V_{IN} - V_{OUT}$            | Dropout Voltage   | $\Delta V_{OUT}$ , $\Delta V_{REF} = 1\%$ , $I_{OUT} = 100mA$          |       | 1.11  | 1.20  | V    |
|                               |                   | $\Delta V_{OUT}$ , $\Delta V_{REF} = 1\%$ , $I_{OUT} = 500mA$          |       | 1.18  | 1.25  | V    |
|                               |                   | $\Delta V_{OUT}$ , $\Delta V_{REF} = 1\%$ , $I_{OUT} = 1A$             |       | 1.26  | 1.30  | V    |
| $I_{CL}$                      | Current Limit     | $V_{IN} - V_{OUT} = 2V$ , $T_J = 25^\circ C$                           | 1.25  | 1.4   | 1.6   | A    |
| Minimum Load Current (Note 1) |                   | Adjustable Version                                                     |       | 5     | 10    | mA   |
| $I_q$                         | Quiescent Current | Fixed<br>$V_{IN} - V_{OUT} = 1.25V$                                    |       | 4     | 8     | mA   |
| $I_{ADJ}$                     | ADJ Pin Current   |                                                                        |       | 55    | 120   | uA   |
| Temperature Stability         |                   |                                                                        |       |       | 0.5   | %    |
| $\theta_{JC}$                 | Thermal Resistor  | SOT-223                                                                |       | 20    |       | °C/  |


### Typical Application



TP1117 adjustable output voltage


$$V_{OUT} = 1.25V(1 + R2/R1)$$

The TP1117 adjustable regulator provide 1.25V reference voltage. Any output voltage between 1.25V~13.8V can be available by choosing two external resistors.





TP1117 fixed output

### Block Diagram




### Typical Characteristics


#### 1. Load Regulation





#### 2. Line Regulation




#### 3. Dropout Voltage



#### 4. Temperature Stability




### 5. ADJ Pin Current vs. Temperature





### 6. Load Transient Response

Load Current Change from 2mA to 500mA



**SOT223 Package Information**



| Symbol   | Dimensions In Millimeters |       | Dimensions In Inches |       |
|----------|---------------------------|-------|----------------------|-------|
|          | Min.                      | Max.  | Min.                 | Max.  |
| A        | —                         | 1.800 | —                    | 0.071 |
| A1       | 0.020                     | 0.100 | 0.001                | 0.004 |
| A2       | 1.500                     | 1.700 | 0.059                | 0.067 |
| b        | 0.660                     | 0.840 | 0.026                | 0.033 |
| $b_1$    | 2.900                     | 3.100 | 0.114                | 0.122 |
| c        | 0.230                     | 0.350 | 0.009                | 0.014 |
| D        | 6.300                     | 6.700 | 0.248                | 0.264 |
| E        | 6.700                     | 7.300 | 0.264                | 0.287 |
| $E_1$    | 3.300                     | 3.700 | 0.130                | 0.146 |
| e        | 2.300(BSC)                |       | 0.091(BSC)           |       |
| L        | 0.750                     | —     | 0.030                | —     |
| $\theta$ | 0°                        | 10°   | 0°                   | 10°   |