



深圳市佑驰电子有限公司

Specification for Approval

产品名称: 一体系列电感

规格型号: TCMC-1090-XXX-M-1A

产品编号:

日期: 2020-01-23

1、本承诺书的内容更改需经过双方确认，任一方单独的修改均视为无效。

2、本承诺书在送达客户后，请给予承认并即签回，如无签回下订单的，我司有权以此承认书标准生产，并表示购买方默认许可。

	审核	制作

批准	审核	检验



REVISION					
REV	DESCRIPTION	DATE	DESIGNED	CHECKED	APPROVED
A0	文件建立	2020/01/23	吕秀秀	Bowen	Darren

High Current, Power Inductors

TCMC-1090-XXX-M-1A Power Choke



■ Description

- AEC-Q200 qualified
- Halogen Free
- 125°C maximum total temperature operation
- 10.4x9.4x11.05mm maximum surface mount package
- Magnetically shielded, low EMI
- High current carrying capacity, Low core losses
- RoHS compliant

■ Applications

- Automotive applications

■ Environmental Data

- Storage temperature range: -55°C to +125 °C
- Operating temperature range: -55°C to +125°C
(ambient plus self-temperature rise)
- Solder reflow temperature: J-STD-020 compliant


■ Product Identification

① ② ③ ④ ⑤

TCMC – 1090 – 150 – M – 1A

- ① Product Series
- ② Dimensions: 10.4x9.4x11.05mm
- ③ Inductance: 150=15.0μH
- ④ Tolerance: M=±20%
- ⑤ Automotive: 1A

■Product Dimension – mm




■Marking


The inductor is marked with a 3-digit code

Example - -15.0→150


Note: Using Laser for marking



■Material List



■Schematics



NO.	Part Name	Material
1	Electrode	Cu+Sn plating C1100R, Sn:6.5±1.5μm
2	Core	Metal composite core
3	Coil	Copper wire, 220°C
4	Epoxy(six side)	Min.0.02mm





■ Electrical Requirements

Part No.	Inductance	DC Resistance		Heating Rating Current	Saturation Current	Rated Voltage
	L0 (μH)	DCR (mΩ)		Idc (A)	Isat (A)	(V)
	±20 %, 100 kHz, 1V	TYP.	MAX.	TYP.	TYP.	Max.
TCMC-1090-3R3-M-1A	3.3	7.5	8.6	9.0	26.0	75
TCMC-1090-100-M-1A	10.0	18.0	22.0	5.8	12.0	75
TCMC-1090-150-M-1A	15.0	34.0	40.8	4.5	9.0	75
TCMC-1090-220-M-1A	22.0	46.0	56.0	3.6	8.5	75

Notes

1. All test data is referenced to 25 °C ambient
2. Operating temperature range - 55 °C to + 125 °C
3. Idc(A):DC current (A) that will cause an approximate ΔT of 40 °C(reference ambient temperature is 25 °C)
4. Isat(A):DC current (A) that will cause L0 to drop approximately 25 %
5. The part temperature (ambient + temp rise) should not exceed 125 °C under worst case operating conditions. Circuit design, component placement, PWB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.

■ Electrical Characteristics


Test Instruments	Test Condition
Wayne kerr 3260B/G LCR Meter Wayne kerr 3265B Bias Current Source	Temperature: $26 \pm 3^{\circ}\text{C}$ Humidity: $< 70\% \text{ RH}$ Frequency: 100 KHz, 1.0V
TCMC-1090-3R3-M-1A 	TCMC-1090-100-M-1A 
TCMC-1090-150-M-1A 	TCMC-1090-220-M-1A 

General characteristics

Mechanical Reliability			
No.	Item	Specification and Requirement	Test Method
1	Solderability	The surface of terminal immersed shall be minimum of 95% covered with a new coating of solder	Retention time: 245 ± 5 °C for 5+0/-0.5seconds;
2	Resistance to Soldering Heat	Change from an initial value Inductance: within $\pm 10\%$	Retention time: within 30 seconds 255 ± 5 °C , Three Times;
3	Terminal Strength	No electrode detachment	No electrode detachment should be found when the device is pushed in two directions of X and Y with the force of 17.7N for 60 seconds after soldering between copper plate and the electrodes;
4	Vibration	Inductance change: Within $\pm 10\%$ Without mechanical damage such as break	1. Vibration frequency: (10 Hz to 2000 Hz to 10Hz) in 20 minutes as a period; 2. Vibration time: Period cycled for four hours in each of 3 mutual perpendicular directions. 3. Amplitude: 1.5 mm max.
5	Mechanical Shock	Inductance change: Within $\pm 10\%$ Without mechanical damage such as break	1. Peak value: 100 G, Duration of pulse: 6ms 2. 3 times in each positive and negative direction of 3 mutual perpendicular directions;
6	Substrate Bending	Inductance change: Within $\pm 10\%$ Without distinct damage in appearance	1. Bending speed is 0.5mm/sec, 2. While the bending width reaches 2mm, keep it for 60 sec
Endurance Reliability			
No.	Item	Specification and Requirement	Test Method
7	Thermal Shock	Inductance change: Within $\pm 10\%$ Without distinct damage in appearance	Repeat 1000 cycles as follow: (-55 ± 2 °C; 30 $\pm$ 3 min) $\rightarrow$ ($+125 \pm 2$ °C , 30 $\pm$ 3 min)
8	Operational Life	Inductance change: Within $\pm 10\%$ Without distinct damage in appearance	Rated current (Idc) Environment condition: 85 °C Duration: 1000 + 4 / -0 hours
9	High Temperature Storage	Inductance change: Within $\pm 10\%$ Without distinct damage in appearance	Store temperature: $+125 \pm 2$ °C, 1000 + 4 / -0 hours;
10	High Temperature&Humidity	Inductance change: Within $\pm 10\%$ Without distinct damage in appearance	85 °C 85%RH ,1000+4/-0 hours;


■Packaging

•Tape Packaging Dimensions




A0	B0	K0	t
9.5 ± 0.10	10.5 ± 0.10	11.35 ± 0.1	0.5 ± 0.05

•Taping dimension and tape direction , Leader ,Trailer, section dimension



Leader section	Min.400mm
Carrier tape start size	Min.100mm
Trailer section size	Min.160mm

• Reel Dimensions




Unit	A	B
mm	24.5 ± 0.2	2.0 ± 0.2

• Peel force of top cover tape

The peel speed shall be about 300mm/minute

The peel force of top cover tape shall be between 0.1 to 1.3 N



• Taping Quantity

Series	1090
PCS/Reel	300