







RoHS



TOTAL HEIGHT	
Code	H
032	3.2
035	3.5
038	3.8




Product No. : TS-073A-□□□□

型号:

产品高度(H):
032=3.2mm
035=3.5mm
038=3.8mm

: 包装方式
-P=编带(非编带, 不启用)
: 弹片
D2=SUS/1PCS
D4=SUS/2PCS

操作力度:
120=120gf±50gf
180=180gf±50gf
250=250gf±50gf



PCB Layout(Pattern side)

⑤	Button		1	LCP	Black
④	Reed		2	SUS	Silver Covered
③	Cover		1	Phosphorus copper	Silvering
②	Base		1	LCP	White
①	Terminal		2	Phosphorus copper	Silvering
NO.	Name	Number	Qty	Materil	Remarks

ZHONGDI®

Zhongdi Electronic Technology Co., Ltd

design
Review
Approved

date
date
date

name
model
TACT SWITCHS
TS-073A-□□-D□

Drawing number:

Proportion 1:1 unit mm gage number A4

modify Review Approved

angle ±2°
10~30 ±0.30
5~10 ±0.20
~ 5 ±0.10
Tolerance not specified

项 目 Item	技术参数 Technical Parameter	标 准 Standard
电气性能 Electrical Properties	额定电流 Rated Current:	50mA
	额定电压 Rated voltage:	DC 12V
	接触电阻 Contact resistance:	≤100mΩ
	绝缘电阻 Insulation Resistance:	DC 250V 1 min ≥100MΩ
	耐压强度 Compressive strength:	AC 250V 50Hz/1 min
机械性能 Mechanical Properties	机械寿命 Mechanical life:	100,000 cycles Min
	操作行程 Operation Stroke:	0.20±0.10mm
环境性能 Environmental	工作温度 Operation temperature:	-25℃~ +75℃
	使用湿度 Use humidity:	≤85% RH
可靠性特性 Reliability Characteristics	回流焊 Reflow Soldering:	≤260℃ 时间 Time 3s
	波峰焊 Wave soldering:	
	手工焊 Manual welding:	≥260℃ 时间 Time 3s
应用领域 Application area	影音产品、电子玩具、数码产品、通讯产品、安防产品等。 Audiovisual products, electronic toys, digital products, communication products, security products, etc	



绝缘电阻测量仪



直流低电阻测试仪




耐电压测试仪



回流焊机



二次元测量仪



高精密寿命测试仪



盐雾测试仪



按键荷重曲线仪

ZHONGDI® 众迪					Zhongdi Electronic Technology Co., Ltd				
design		date			name	TACT SWITCHS			
Review		date							
Approved		date			name	TS-073A-□□-D□			
number:									

modify	Review	Approved	Tolerance not specified	Proportion	1:1	unit	mm	gape number	A4
--------	--------	----------	-------------------------	------------	-----	------	----	-------------	----