

FEATURES

- Fe base metal material core provides large saturation current
- Metallization on ferrite core results in excellent shock resistance and damage-free durability
- Closed magnetic circuit design reduces leakage flux and Electro Magnetic Interference (EMI)
- Low DCR decreases power loss, small and slim take up less PCB real estate
- Automatic production ensures high quality and consistency
- Operate temperature range $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$ (Including self temp. rise)
- RoHS compliant



APPLICATIONS

- Smart phone, set top box, VR, AR
- Notebooks, desktop computers, servers
- Portable gaming devices, personal navigation systems, personal multimedia devices


PRODUCT IDENTIFICATION

CPN 3012 H 2R2 M T

① ② ③ ④ ⑤ ⑥

- ① Series Name: Metal Alloy Wire Wound SMD Power Inductors
- ② Size Code: L*W*T
- ③ Feature Type: H
- ④ Initial inductance value: 2R2 = 2.2uH
- ⑤ Inductance Tolerance: M \pm 20%
- ⑥ Packing: Tape & Reel

SHAPE AND DIMENSIONS [mm]



Recommended Land Pattern

Series	A	B	C	D	E	F	a Typ.	b Typ.	c Typ.
CPN3012H	3.0 \pm 0.2	3.0 \pm 0.2	1.35 Max.	2.5 \pm 0.2	0.9 Typ.	1.2 Typ.	1.00	1.10	2.7

Electrical Characteristics List

Part Number	Inductance	DC Resistance		Isat(A)		Irms(A)	
	1MHz/0.1V	Max.	Typ.	Max.	Typ.	Max.	Typ.
Units	(uH)	Ω	Ω	A	A	A	A
CPN3012HR47NT	0.47 \pm 30%	0.033	0.028	6.80	8.00	3.90	4.30
CPN3012H1R0NT	1.0 \pm 30%	0.054	0.049	4.20	5.20	2.70	3.10
CPN3012H1R5NT	1.5 \pm 30%	0.074	0.067	3.40	4.10	2.50	2.90
CPN3012H2R2MT	2.2 \pm 20%	0.108	0.098	2.80	3.35	2.05	2.35
CPN3012H3R3MT	3.3 \pm 20%	0.155	0.135	2.20	2.60	1.70	2.00
CPN3012H4R7MT	4.7 \pm 20%	0.235	0.217	2.00	2.50	1.30	1.70
CPN3012H6R8MT	6.8 \pm 20%	0.340	0.253	1.60	1.90	1.10	1.25
CPN3012H100MT	10.0 \pm 20%	0.432	0.374	1.20	1.45	1.00	1.15

Note:※1: Rated current: Isat(max.)or Irms(max.),whichever is smaller;

※2: Saturation Current: Max. Value, DC current at which the inductance drops less than 30% from its value without current; Typ. Value, DC current at which the inductance drops 30% from its value without current;


※3: Irms: DC current that causes the temperature rise (ΔT) from 20℃ ambient.

For Max. Value, $\Delta T < 40^{\circ}\text{C}$; for Typ. Value, ΔT is approximate 40°C .

The part temperature (ambient + temp. rise) should not exceed 125°C under worst case operating conditions. Circuit design, component placement, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.

Absolute Maximum Voltage : DC 40V

Structure



NO	Components	Material
①	Core	soft magnetic metal
②	Wire	Polyurethane system enameled copper wire
③	Magnetic Glue	Epoxy resin and magnetic powder
④	Plating	AgNiSn or FeNiCu + Sn Alloy

Reliability Test

TEST ITEM	SPECIFICATION	TEST CONDITION
Withstanding voltage test	After test, inductors shall have no evidence of electrical and mechanical damage.	AC voltage of 100v and AC current of 1mA applied between inductor's terminal and core for 3 secs.
Resistance to soldering heat	1. Inductor shall have no eviden of electrical and mechanical damage. 2. Inductance shall not chan more than $\pm 5\%$. 3. Q shall not change more than 20%.	a. Temp: 260 ± 5 b. Time: 10 ± 1.0 se
Solderability test	The terminal shall be at least 95% covered with solder.	After fluxing, the terminal shall be dipped in a melted solder bath at $245 \pm 5^\circ\text{C}$ for 4 ± 1.0 secs.
High temperature & high humidity test	The anti-erosion quality of the surface and the specimen's inductance shall not change from the initial value within $\pm 10\%$	a. Test conditi 1)Temp.: 85°C , R.H.:85% 2)Time: 144 ± 2 hours b. Measurement method The experimental component should be put at normal condition for 2 hours then to measure again after test
Salt spray test		a. Test conditi 1)Temp.: $35 \pm 2^\circ\text{C}$ 2)Time: 48 ± 2 hours 3)Salt solution PH:6.5~7.2 b. Measurement method The experimental component should be put at normal condition for 2 hours then to measure again after test
Vibration test	1. Inductance shall be within 10% of the initial value. 2. Appearance: no dama	a. Frequency: 10 to 55 b. Amplitude: 1.5 c. Direction and tim X, Y and Z directions for 2 hours each.

TEST ITEM	SPECIFICATION	TEST CONDITION
Free fall test	No mechanical damage shall be noticed.	Drop 5 times on a concrete floor from 1m the height
Temperature Cycling test	1. Inductance shall be within 10% of the initial value 2. Appearance: No damage	a. Test condition 1) Temp.: -55°C , time: 30 ± 3 min 2) Temp.: $+125^{\circ}\text{C}$, time: 30 ± 3 min 3) Cycles times: 12 cycles b. Measurement method The experimental component should be put at normal condition for 2 hours then to measure again after test
High Temperature resistance test		a. Test condition 1) Applied rated current 2) Temp.: $85^{\circ}\text{C} \pm 2^{\circ}\text{C}$ 3) Test time: $1000 \pm 24/-0$ H b. Measurement method The experimental component should be put at normal condition for 24 hours then to measure again after test.
Low temperature resistance test		a. Test condition 1) Temp.: $-55^{\circ}\text{C} \pm 2^{\circ}\text{C}$ 2) Test time: $1000 \pm 24/-0$ H b. Measurement method The experimental component should be put at normal condition for 24 hours then to measure again after test.

We have suggested the storage period of lead-free product should not over 6 months.


PACKAGING(unit: mm)

1.包装类型：编带装


2.包装尺寸：

☐ 13" 盘



☒ 7" 盘



	13" 盘	7" 盘
A	$\Phi 330\pm 2.0$	$\Phi 178\pm 2.0$
D	8.5	



Item	W	A0	B0	K0	P	T	E	F	D0	P0
(mm)	8.0 ± 0.3	3.3 ± 0.15	3.3 ± 0.15	1.4 ± 0.1	4.0 ± 0.1	0.3 ± 0.1	1.75 ± 0.1	3.5 ± 0.1	1.5 ± 0.1	4.0 ± 0.1



每卷	2000	Pcs
----	------	-----

每盒	4卷,共	8000	Pcs
----	------	------	-----

每箱	6盒,共	48000	Pcs
----	------	-------	-----

Re-flowing Profile:

