


**Features**

- Super Low Gate Charge
- Green Device Available
- Excellent Cdv/dt effect decline
- Advanced high cell density Trench technology
- 100% EAS Guaranteed

Bvdss**30V****Rdson****6.5mΩ****ID****60A****Application**


- PWM applications
- Load Switch
- Power management

RoHS**Package**

Marking and pin assignment



TO252-3L top view



Schematic diagram

Package Marking and Ordering Information

Device Marking	Device	Device Package	Quantity
60N03	60N03	TO252-3L	2500

Absolute Maximum Ratings ($T_C=25^{\circ}\text{C}$ unless otherwise specified)

Parameter		Symbol	Value	Unit
Drain-Source Voltage		V_{DS}	30	V
Gate-Source Voltage		V_{GS}	± 20	V
Continuous Drain Current, $V_{GS}=10\text{V}^1$	$T_C=25^{\circ}\text{C}$	I_D	60	A
	$T_C=100^{\circ}\text{C}$		33	A
Pulsed Drain Current ²		I_{DM}	198	A
Avalanche Current		I_{AS}	53.8	A
'Single Pulsed Avalanche Energy ³		EAS	36	mJ
Power Dissipation	$T_C=25^{\circ}\text{C}$	P_D	32.5	W
Operating and Storage Temperature Range		T_J, T_{STG}	-55 ~ 175	$^{\circ}\text{C}$

Thermal Resistance Ratings

Parameter	Symbol	Value	Max.	Unit
Thermal Resistance Junction-Case ¹	$R_{\theta JC}$	-	3.56	$^{\circ}\text{C/W}$



Ordering Information

Ordering Number	Package	Pin Assignment			Packing
Halogen Free		G	D	S	
HL60N03	TO-252	1	2	3	Tape Reel

Electrical Characteristics ($T_J=25^{\circ}\text{C}$ unless otherwise noted)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit	
Drain-Source Breakdown Voltage	BV_{DSS}	$I_D=250\mu A, V_{GS}=0V$	30	-	-	V	
Drain-Source Leakage Current	I_{DSS}	$V_{DS}=30V, V_{GS}=0V$	-	-	1	μA	
Gate-Source Leakage Current	I_{GSS}	$V_{GS}=\pm 20V, V_{DS}=0V$	-	-	± 100	nA	
Gate Threshold Voltage	$V_{GS(th)}$	$V_{GS}=V_{DS}, I_D=250\mu A$	1	1.5	2.5	V	
Static Drain-Source On-Resistance ³	$R_{DS(on)}$	$V_{GS}=10V, I_D=25A$	-	6.5	7.5	m Ω	
		$V_{GS}=4.5V, I_D=15A$	-	10	14		
Input Capacitance	C_{iss}	$V_{DS}=15V, V_{GS}=0V, f=1MHz$	-	1140	-	pF	
Output Capacitance	C_{oss}		-	175	-		
Reverse Transfer Capacitance	C_{rss}		-	151	-		
Total Gate Charge	Q_g	$V_{GS}=15V, V_{DS}=10V, I_D=25A$	-	13.3	-	nC	
Gate-Source Charge	Q_{gs}		-	3.1	-		
Gate-Drain Charge	Q_{gd}		-	5	-		
Turn-On Delay Time	$t_{d(on)}$	$V_{GS}=10V, V_{DS}=15V,$ $I_D=25A, R_G=3\Omega$	-	15	-	ns	
Turn-On Rise Time	t_r		-	19	-		
Turn-Off Delay Time	$t_{r(off)}$		-	35	-		
Turn-Off Fall Time	t_f		-	21	-		
Maximum Continuous Drain to Source Diode Forward Current		I_S	-	-	50	A	
Maximum Pulsed Drain to Source Diode Forward Current		I_{SM}	-	-	200	A	
Diode Forward Voltage	$V_{GS}=0V, I_S=30A$		V_{SD}	-	-	1.2	V
Reverse Recovery Time	$I_F=30A, dI/dt=100A/\mu s$		t_{rr}	-	25	-	ns
Reverse Recovery Charge			Q_{rr}	-	26	-	nC

Notes:

1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature
2. EAS condition: $T_J=25^{\circ}\text{C}$, $V_{DD}=15\text{V}$, $V_G=10\text{V}$, $R_G=25\Omega$, $L=0.5\text{mH}$, $I_{AS}=12\text{A}$
3. Pulse Test: Pulse Width $\leq 300\mu\text{s}$, Duty Cycle $\leq 0.5\%$



Typical Performance Characteristics

Figure 1: Output Characteristics




Figure 2: Typical Transfer Characteristics




Figure 3: On-resistance vs. Drain Current




Figure 4: Body Diode Characteristics




Figure 5: Gate Charge Characteristics




Figure 6: Capacitance Characteristics






Figure 7: Normalized Breakdown Voltage vs. Junction Temperature




Figure 8: Normalized on Resistance vs. Junction Temperature





Figure 9: Maximum Safe Operating Area



Maximum Effective Transient Thermal Impedance, Junction-to-Case






Figure 10: Maximum Continuous Drain Current vs. Case Temperature






Package Mechanical Data TO252-3L



Ref.	Dimensions					
	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	2.10		2.50	0.083		0.098
A2	0		0.10	0		0.004
B	0.66		0.86	0.026		0.034
B2	5.18		5.48	0.202		0.216
C	0.40		0.60	0.016		0.024
C2	0.44		0.58	0.017		0.023
D	5.90		6.30	0.232		0.248
D1	5.30REF			0.209REF		
E	6.40		6.80	0.252		0.268
E1	4.63			0.182		
G	4.47		4.67	0.176		0.184
H	9.50		10.70	0.374		0.421
L	1.09		1.21	0.043		0.048
L2	1.35		1.65	0.053		0.065
V1		7°			7°	
V2	0°		6°	0°		6°



Ref.	Dimensions					
	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
W	15.90	16.00	16.10	0.626	0.630	0.634
E	1.65	1.75	1.85	0.065	0.069	0.073
F	7.40	7.50	7.60	0.291	0.295	0.299
D0	1.40	1.50	1.60	0.055	0.059	0.063
D1	1.40	1.50	1.60	0.055	0.059	0.063
P0	3.90	4.00	4.10	0.154	0.157	0.161
P1	7.90	8.00	8.10	0.311	0.315	0.319
P2	1.90	2.00	2.10	0.075	0.079	0.083
A0	6.85	6.90	7.00	0.270	0.271	0.276
B0	10.45	10.50	10.60	0.411	0.413	0.417
K0	2.68	2.78	2.88	0.105	0.109	0.113
T	0.24		0.27	0.009		0.011
t1	0.10			0.004		
10P0	39.80	40.00	40.20	1.567	1.575	1.583



Important Notice and Disclaimer

HL Microelectronics reserves the right to make changes to this document and its products and specifications at any time without notice.

Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

HL Microelectronics makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, not does HL Microelectronics assume any liability for application assistance or customer product design.

HL Microelectronics does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of HL Microelectronics.

HL Microelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of HL Microelectronics.