



1.Configuration & Dimensions : (Unit:mm)



SYMBOL	A	B	C	D	E	F	G	Q'Ty/Disc
ADT130806	17.0Max	11.0Max	10.0 ±2.0	0.55±0.1	8.0Ref	7.0Ref	1.5Max	100

2.Electrical Schematics



Winding order	Origination	Parameter
N1	1—4	2UEWΦ0.55mm*23.5TS Ref
N2	2—3	2UEWΦ0.55mm*23.5TS Ref

3.Part Number Code

ADT 130806 X 602 - GA2
 A B C D E

A: Series Name Power Chokes
 B: Dimensions(mm) 13: 17.0*11.0*10.0
 C: Tolerance X: Min
 D: Inductance 602=6.0mH
 E: Internal controls

4.Electrical Characteristics

Part Number	Inductance (mH)	Tolerance	Test Frequency (Hz)	DC Resistance (mΩ)Max.	Current (A)Max.
ADT130806X602-GA2	6.0	Min	1KHz/0.25V	90.0	4.0

Notes:

- 1) All test data is referenced to 25°C ambient.
- 2) Operating temperature range -25°C to +105°C,(Including self - temperature rise).
- 3) Coil to Coils Test Conditions : AC 50Hz,1000V,5mA, 3 Sec.