

## Power MOSFET Wafer ( N-Type 60 V )

### ● Features

Advanced trench cell design


Extremely low threshold voltage

$BV \geq 60\text{ V}$      $R_{DS(ON)} \leq 75\text{ m}\Omega @ V_{GS} = 10\text{ V}$

$R_{\theta t} \leq 1.4\text{ W}$      $R_{DS(ON)} \leq 82\text{ m}\Omega @ V_{GS} = 5\text{ V}$

$I_D \leq 3.5\text{ A}$      $R_{DS(ON)} \leq 90\text{ m}\Omega @ V_{GS} = 4.5\text{ V}$


### Simplified Outline



SOT-89

1. GATE 2. DRAIN 3. SOURCE

### Symbol



### ● Applications

Portable appliances

High speed switch

Battery management

### ● Limiting Values

| Symbol          | Parameter                | Conditions                                              | Min  | Max      | Unit             |
|-----------------|--------------------------|---------------------------------------------------------|------|----------|------------------|
| $V_{DS}$        | Drain-Source Voltage     | $T_A = 25\text{ }^\circ\text{C}$                        | 60   | -        | V                |
| $V_{GS}$        | Gate-Source Voltage      | $T_A = 25\text{ }^\circ\text{C}$                        | -    | $\pm 20$ | V                |
| $I_D^*$         | Drain Current ( DC )     | $T_A = 25\text{ }^\circ\text{C}, V_{GS} = 10\text{ V}$  | -    | 3.5      | A                |
|                 |                          | $T_A = 100\text{ }^\circ\text{C}, V_{GS} = 10\text{ V}$ | -    | 2.2      | A                |
| $I_{DM}^{*,**}$ | Drain Current ( Pulsed ) | $T_A = 25\text{ }^\circ\text{C}, V_{GS} = 10\text{ V}$  | -    | 14       | A                |
| $P_{tot}^*$     | Total Power Dissipation  | $T_A = 25\text{ }^\circ\text{C}$                        | -    | 1.4      | W                |
| $T_{stg}$       | Storage Temperature      |                                                         | - 55 | 150      | $^\circ\text{C}$ |
| $T_J$           | Junction Temperature     |                                                         | - 55 | 150      | $^\circ\text{C}$ |
| $I_S$           | Diode Forward Current    | $T_A = 25\text{ }^\circ\text{C}$                        | -    | 3.5      | A                |

Notes :

\* Surface Mounted on 1 in<sup>2</sup> pad area,  $t \leq 10\text{ sec}$

\*\* Pulse width  $\leq 300\text{ }\mu\text{s}$ , duty cycle  $\leq 2\%$

● Electrical Characteristics ( Ta = 25 °C Unless Otherwise Noted )


| Symbol                                   | Parameter                      | Conditions                                                                                                                  | Min | Typ  | Max   | Unit |
|------------------------------------------|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------|-----|------|-------|------|
| Static Characteristics                   |                                |                                                                                                                             |     |      |       |      |
| BV <sub>DSS</sub>                        | Drain-Source Breakdown Voltage | V <sub>GS</sub> = 0 V, I <sub>DS</sub> = 250 μA                                                                             | 60  | -    | -     | V    |
| V <sub>GS(th)</sub>                      | Gate Threshold Voltage         | V <sub>DS</sub> = V <sub>GS</sub> , I <sub>DS</sub> = 250 μA                                                                | 1   | -    | 2     | V    |
| I <sub>DSS</sub>                         | Drain Leakage Current          | V <sub>DS</sub> = 48 V, V <sub>GS</sub> = 0 V                                                                               | -   | -    | 1     | μA   |
| I <sub>GSS</sub>                         | Gate Leakage Current           | V <sub>GS</sub> = ± 20 V, V <sub>DS</sub> = 0 V                                                                             | -   | -    | ± 100 | nA   |
| R <sub>DS(ON)</sub> <sup>a</sup>         | On-State Resistance            | V <sub>GS</sub> = 10 V, I <sub>DS</sub> = 2 A                                                                               | -   | 60.6 | 72.8  | mΩ   |
|                                          |                                | V <sub>GS</sub> = 4.5 V, I <sub>DS</sub> = 1 A                                                                              | -   | 69.2 | 90    |      |
| Diode Characteristics                    |                                |                                                                                                                             |     |      |       |      |
| V <sub>SD</sub> <sup>a</sup>             | Diode Forward Voltage          | I <sub>SD</sub> = 2 A, V <sub>GS</sub> = 0 V                                                                                | -   | -    | 1.3   | V    |
| t <sub>rr</sub>                          | Reverse Recovery Time          | I <sub>SD</sub> = 2 A, dI <sub>SD</sub> / dt = 100 A / μs                                                                   | -   | 9    | -     | nS   |
| Q <sub>rr</sub>                          | Reverse Recovery Charge        |                                                                                                                             | -   | 5.1  | -     | nC   |
| Dynamic Characteristics <sup>b</sup>     |                                |                                                                                                                             |     |      |       |      |
| C <sub>iss</sub>                         | Input Capacitance              | V <sub>GS</sub> = 0 V, V <sub>DS</sub> = 30 V<br>Frequency = 1 MHz                                                          | -   | 498  | -     | pF   |
| C <sub>oss</sub>                         | Output Capacitance             |                                                                                                                             | -   | 25   | -     |      |
| C <sub>rss</sub>                         | Reverse Transfer Capacitance   |                                                                                                                             | -   | 21   | -     |      |
| t <sub>d(on)</sub>                       | Turn-on Delay Time             | V <sub>DS</sub> = 30 V, V <sub>GEN</sub> = 10 V,<br>R <sub>G</sub> = 3.9 Ω, R <sub>L</sub> = 15 Ω,<br>I <sub>DS</sub> = 2 A | -   | 4.3  | -     | nS   |
| t <sub>r</sub>                           | Turn-on Rise Time              |                                                                                                                             | -   | 2.7  | -     |      |
| t <sub>d(off)</sub>                      | Turn-off Delay Time            |                                                                                                                             | -   | 14   | -     |      |
| t <sub>f</sub>                           | Turn-off Fall Time             |                                                                                                                             | -   | 5.7  | -     |      |
| Gate Charge Characteristics <sup>b</sup> |                                |                                                                                                                             |     |      |       |      |
| Q <sub>g</sub>                           | Total Gate Charge              | V <sub>GS</sub> = 10 V, V <sub>DS</sub> = 30 V,<br>I <sub>DS</sub> = 2 A                                                    | -   | 9.5  | -     | nC   |
| Q <sub>gs</sub>                          | Gate-Source Charge             |                                                                                                                             | -   | 2.2  | -     |      |
| Q <sub>gd</sub>                          | Gate-Drain Charge              |                                                                                                                             | -   | 1.1  | -     |      |

Notes : a : Pulse test ; pulse width  $\leq 300\text{ }\mu\text{s}$ , duty cycle  $\leq 2\%$


b : Guaranteed by design, not subject to production testing

## Typical Characteristics


Power Capability




Current Capability




Operating




Transient Thermal Impedance




## Output Characteristics




## On Resistance







## Transfer Characteristics




## Normalized Threshold Voltage






## SOT-89 Package Outline Dimensions



| Symbol | Dimensions In Millimeters |       | Dimensions In Inches |       |
|--------|---------------------------|-------|----------------------|-------|
|        | Min                       | Max   | Min                  | Max   |
| A      | 1.400                     | 1.600 | 0.055                | 0.063 |
| b      | 0.320                     | 0.520 | 0.013                | 0.020 |
| b1     | 0.400                     | 0.580 | 0.016                | 0.023 |
| c      | 0.350                     | 0.440 | 0.014                | 0.017 |
| D      | 4.400                     | 4.600 | 0.173                | 0.181 |
| D1     | 1.550 REF.                |       | 0.061 REF.           |       |
| E      | 2.300                     | 2.600 | 0.091                | 0.102 |
| E1     | 3.940                     | 4.250 | 0.155                | 0.167 |
| e      | 1.500 TYP.                |       | 0.060 TYP.           |       |
| e1     | 3.000 TYP.                |       | 0.118 TYP.           |       |
| L      | 0.900                     | 1.200 | 0.035                | 0.047 |

## SOT-89 Suggested Pad Layout



Note:

1. Controlling dimension: in millimeters.
2. General tolerance:  $\pm 0.05\text{mm}$ .
3. The pad layout is for reference purposes only.