





HSF



RoHS



PCB Layout Diagram
Top View

NOTE:

1, Material:

a. Housing: LCP UL94V-0

Contact: Phosphor Bronze

(Surface Plating: Sn=100u"~120u")

See Ordering Information

2, Electric:

a. Contact Resistance: 30 Milliohms Max

b. Insulation Resistance: 1000 MEGA OHMS Min

c. Dielectric Voltage: 500V AC One Sea Level

d. Operating Temperature: -55° To 105°

Order code:

BT — M — SN — R — CR2032I
① ② ③ ④ ⑤

① BT: Coin Cell Holders ③ Contact Plating

② Apperance for the product

M: SMT TYPE

SN: Tin

G0: Gold flash

G1: 3U" Gold

G2: 5U" Gold

G3: 10U" Gold

G4: 15U" Gold

G5: 30U" Gold

④ Packing method

A: Tray packing


R: Tape & reel packing

⑤ Product number

CR2032I

Unless Otherwise specified tolerance
X. ±0.35 X.XX: ±0.20
X.X: ±0.25 X.XXX: ±0.15

SCALE: As Shown UNIT: mm
DRAW Mo Guo Xuan DATE 03/14/2019
CHECK BobYang DATE 03/14/2019



TITLE: Coin Cell Holders For CR2032

DRAWING NO: BT-M-SN-R-CR2032I

PRODUCT NO: BT-M-SN-R-CR2032I

REV	DESCRIPTION	DATE
1		
2		
3		
4		
5		