





HSF



RoHS



PCB Layout Diagram
Top View

Note:

1. Material:

- a. Housing: Thermoplastic Glass Fibre UL94V-0
- b. Contact: Phosphor Bronze (Surface Plating Au)
See Ordering Information

2. Electric:

- a. Contact Resistance: 30 Milliohms Max.
- b. Insulation Resistance: 1000 Mega Ohms Min.
- c. Dielectric Voltage: 500 V AC One Sec Level
- d. Operating Temperature: -55° To +105°

Order code:

BT — S — G0 — A — CR2032F
① — ② — ③ — ④ — ⑤

① BT: Coin Cell Holders

② Appearance for the product


S: 180 TYPE

③ Contact Plating
SN: Tin

- G0: Gold flash
- G1: 3U" Gold
- G2: 5U" Gold
- G3: 10U" Gold
- G4: 15U" Gold
- G5: 30U" Gold


④ Packing method
A: Tray packing
R: Tape & reel packing

⑤ Product number
CR2032F



Unless Otherwise specified tolerance
X. ±0.35 X.XX: ±0.20
X.X: ±0.25 X.XXX: ±0.15

SCALE: As Shown UNIT: mm
DRAW Wu Feng Rong DATE 07/05/2020
CHECK BobYang DATE 07/05/2020



TITLE:
Coin Cell Holders For CR2032

DRAWING NO: BT-S-G0-A-CR2032F

PRODUCT NO: BT-S-G0-A-CR2032F

Delete Dimensions

change BT-S-G0-CR2032-12 to BT-S-G0-A-CR2032F

REV DESCRIPTION

08/02/2022

01/13/2019

DATE