






RoHS



NOTE:

1. Rating: 24V 25mA DC
2. Insulation Resistance: $\geq 100 \text{ M}\Omega$
3. Withstand voltage: AC 500V 1Minute
4. Operating Force Range: 1000gf Max
5. Mechanical Life: 3,000 Cycles

(F)	Dust film		1	Polyimide tape	
(E)	Terminal		16	Phosphor bronze	Gold plating
(D)	Contact spring		8	Phosphor bronze	Gold plating
(C)	Handle		8	PA46	White
(B)	Cover		1	PPS	Black
(A)	Base		1	PPS	Black
NO.	Name	Number	Qty	Materil	Remarks



Zhongdi Electronic Technology Co., Ltd

design	date	name	DIP SWITCH
Review	date	model	DSHP-08
Approved	date		

Drawing number:

modify	Review	Approved	Tolerance not specified	Proportion	1:1	unit	mm	gape number	A4
--------	--------	----------	-------------------------	------------	-----	------	----	-------------	----