

■ Features

- Glass passivated chip
- Low reverse leakage current
- High surge current capability
- Fast reverse recovery time

■ Applications

- General purpose use in AC/DC bridge full wave rectification

■ Mechanical Data

- Case: MSB
- Polarity symbols being marked on body
- Molding compound meets UL 94V-0 flammability rating
- RoHS-compliant, Solder plated, solderable per MIL-STD-750, Method 2026



Reverse Voltage

50-1000 V

Forward Current

4.0 A max

Appearance Image



■ Marking

- RMSB40(A~M)

■ Maximum Ratings @ Ta = 25°C unless otherwise noted

PARAMETER	SYMBOL	UNIT	RMSB40A	RMSB40B	RMSB40D	RMSB40G	RMSB40J	RMSB40K	RMSB40M
Repetitive peak reverse voltage	V _{RRM}	V	50	100	200	400	600	800	1000
Maximum RMS voltage	V _{RMS}	V	35	70	140	280	420	560	700
Maximum DC blocking Voltage	V _{DC}	V	50	100	200	400	600	800	1000
Maximum average output current@60Hz sine wave, resistance load	I _{F(AV)}	A	4.0						
Peak forward surge current 8.3 ms single half sine wave superimposed on rated load	I _{FSM}	A	120						
Peak forward surge current 1.0 ms single half sine wave superimposed on rated load		A	240						
Current squared time @1ms≤t<8.3ms T _j =25°C, Rating of per diode	I ² t	A ² S	59.76						
Maximum reverse recovery time	T _{rr}	ns	150				250	500	
Storage temperature	T _{stg}	°C	-55~+150						
Junction temperature	T _j	°C	-55~+150						

■ Electrical Characteristics @ Ta = 25°C unless otherwise noted

PARAMETER	TEST CONDITIONS	SYMBOL	UNIT	RMSB40A	RMSB40B	RMSB40D	RMSB40G	RMSB40J	RMSB40K	RMSB40M
Maximum instantaneous forward voltage	$I_F=2.0A$	V_F	V	1.3						
Maximum DC reverse current at rated DC blocking voltage	$V_R=V_{DC}$, Tj=25°C	I_R	μA	5						
	$V_R=V_{DC}$, Tj=100°C	I_R		100						

■ Characteristic Curve (Typical)




FIG1. Derating Curve For Output Rectified Current




FIG2. Surge Forward Current Capability




FIG3. Typical Forward Characteristics




FIG4. Typical Reverse Characteristics

Marking and packet information



MB***: Product Type Code **TOS**: Brand Logo

Packaging information	
Reel	3000PCS
Carton	54000PCS
Reel Size	13"

MSB Package outline dimensions

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	1.3	1.5	0.051	0.059
C	0.17	0.29	0.007	0.012
D	6.2	7.0	0.244	0.276
E	7.1	7.6	0.280	0.299
E1	8.4	8.9	0.331	0.350
L	1.0	1.6	0.032	0.055
e	4.9	5.3	0.193	0.209
b	0.95	1.15	0.037	0.045
θ	10°			

Notice

XILONG reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein.
xilong does not assume any liability arising out of the application or use of any product described herein.