



RoHS Compliant



NOTES:

*HOUSING:PBT+30%G/F UL94V-0 color:BLACK

*CONTACT:BRASS T=0.3

*SHELL: SPCC T=0.3

*SCREW:SPCC

*GROUNDING:SPCC T=0.5

*ELECTRIC CHARACTERISTICS:

CONTACT CURRENT RATING: 3.0A MAX.;

CONTACT VOLTAGE RATING:100V DC;

CONTACT RESISTANCE: 30mΩ MAX.;

DIELECTRIC WITHSTANDING VOLTAGE:500V AC/60S;

INSULATION RESISTANCE: 1000 MΩ MIN.AT DC 500V .

*MECHANICAL CHARACTERISTICS:

DURABILITY: 5000 CYCLES.

INSERTION AND EXTRACTION FORCE:

INSERTION FORCE: 50N MAX.

EXTRACTION FORCE: 15N MIN.

*ENVIRONMENT CHARACTERISTICS:

OPERATING TEMPERATURE: -25℃~+70℃

HUMIDITY:45-85% RH.

CONTACT:UNDER PLATED 50u MIN Ni



OVER ALL 100u MIN TIN IN SOLDERING AREA OR CONTACT AREA

SHELL: UNDER PLATED 50u MIN Cu.Over All 80u MIN NICKEL

SCREW: UNDER PLATED 50u MIN Cu.OVER ALL 80u MIN NICKEL

GROUNDING:UNDER PLATED 50u MIN Cu.

UNDER PLATED 50u MIN NICKEL. OVER ALL 100u MIN TIN IN SOLDERING AREA.



PCB Holes Diagram(Top View)

深圳市敏连达科技有限公司 Shenzhen Minlianda Technology Co.,Ltd.		品名(ITEM NO)	HDR-15母 直锁型8.89 蓝色		
		料号(PART NO)	MLD-HDR15PF-8.89BL		
单位(UNIT): MM	未注公差 TOLERANCE UNSPECIFIED	版次(REV): A/0	页次(PAGE):1/1	设计 (DESIGN)	柯南
比例(SCALE) 1:1	X.X ± 0.38 X.XX ± 0.20 X.XXX ± 0.10 X" ± 5" X.X" ± 2"	模号 (MODEL NO)	MLD-2509031032	审核 (CHECKED)	邱敏
		图号 (DWG NO)		核准(APPROVED)	陈镇