






RoHS



NOTE:
1.Rating: 24V 25mA DC
2.Insulation Resistance: $\geq 100 \text{ M}\Omega$
3.Withstand voltage: AC 500V 1Minute
4.Operating Force Range: 1000gf Max
5.Mechanical Life: 3,000 Cycles

Ⓕ	Dust film		1	Polyimide tape	
Ⓖ	Terminal		10	Phosphor bronze	Gold plating
Ⓓ	Contact spring		5	Phosphor bronze	Gold plating
Ⓒ	Handle		5	PA46	White
Ⓑ	Cover		1	PPS	Black
Ⓐ	Base		1	PPS	Black
NO.	Name	Number	Qty	Materil	Remarks

ZHONGDI® Zhongdi Electronic Technology Co., Ltd

design	date	name	DIP SWITCH
Review	date	model	DSHP-05
Approved	date		

Drawing number: A4

modify Review Approved Tolerance not specified Proportion 1:1 unit mm gage number