






RoHS



NOTE:

- 1.Rating: 24V 25mA DC
- 2.Insulation Resistance: $\geq 100 \text{ M}\Omega$
- 3.Withstand voltage: AC 500V 1Minute
- 4.Operating Force Range: 1000gf Max
- 5.Mechanical Life: 3,000 Cycles

(F)	Dust film		1	Polyimide tape	
(E)	Terminal		2	Phosphor bronze	Gold plating
(D)	Contact spring		1	Phosphor bronze	Gold plating
(C)	Handle		1	PA46	White
(B)	Cover		1	PPS	Black
(A)	Base		1	PPS	Black
NO.	Name	Number	Qty	Materil	Remarks

ZHONGDI
众迪

Zhongdi Electronic Technology Co., Ltd

design	date	name	DIP SWITCH
Review	date	model	DSHP-01
Approved	date		

Drawing number:

modify Review Approved Tolerance not specified Proportion 1:1 unit mm gage number A4