





RoHS Compliant



PCB Holes Diagram(Top View)

NOTES:

*HOUSING:PBT+30%G/F UL94V-0 color:BLACK

*CONTACT:BRASS T=0.3

*SHELL: SPCC T=0.3

*SCREW:SPCC

*GROUNDING:SPCC T=0.5

*ELECTRIC CHARACTERISTICS:

CONTACT CURRENT RATING: 3.0A MAX.;

CONTACT VOLTAGE RATING:100V DC;

CONTACT RESISTANCE: 30mΩ MAX.;

DIELECTRIC WITHSTANDING VOLTAGE:500V AC/60S;

INSULATION RESISTANCE: 1000 MΩ MIN.AT DC 500V .

*MECHANICAL CHARACTERISTICS:

DURABILITY: 5000 CYCLES.

INSERTION AND EXTRACTION FORCE:

INSERTION FORCE: 50N MAX.

EXTRACTION FORCE: 15N MIN.

*ENVIRONMENT CHARACTERISTICS:

OPERATING TEMPERATURE: -25℃~+70℃

HUMIDITY:45-85% RH.

CONTACT:UNDER PLATED 50u MIN Ni

OVER ALL 100u MIN TIN IN SOLDERING AREA OR

CONTACT AREA

SHELL: UNDER PLATED 50u MIN Cu.Over All 80u

MIN NICKEL

SCREW: UNDER PLATED 50u MIN Cu.OVER ALL

80u MIN NICKEL

GROUNDING:UNDER PLATED 50u MIN Cu.

UNDER PLATED 50u MIN NICKEL. OVER ALL

100u MIN TIN IN SOLDERING AREA.

深圳市敏连达科技有限公司

Shenzhen Minlianda Technology Co.,Ltd.

品名(ITEM NO) HDR-15母 直锁型8.89 黑色

料号(PART NO) MLD-HDR15PF-8.89B

单位(UNIT): MM

未注公差
TOLERANCE UNSPECIFIED

版次(REV): A/0

页次(PAGE):1/1

设计 (DESIGN)

柯南


比例(SCALE) 1:1

X.X ± 0.38
X.XX ± 0.20
X.XXX ± 0.10
X" ± 5"
X.X" ± 2"

模号 (MODEL NO)

审核 (CHECKED)

邱敏



图号 (DWG NO)

MLD-2509031032

核准(APPROVED)

陈镇