



Description

The PC814X1CSZ9F is a photoelectric coupler composed of two light-emitting diode and phototransistor. It is packaged in a 4-pin package DIP.



Features

- Current transfer ratio:20~300% ($I_F = 5\text{mA}$, $V_{CE} = 5\text{V}$)
- High isolation voltage between input and output($V_{ISO}=5000\text{ Vrms}$)
- Collector - emitter breakdown voltage $BV_{CEO}\geq 80\text{V}$

Applications

- Switching power supply, intelligent meter
- Industrial control, measuring instruments
- Office equipment such as copiers
- Household appliances: such as air conditioners, fans, water heaters, etc.

Schematic Diagram and Package



Absolute Maximum Ratings ($T_a=25^{\circ}\text{C}$)

Parameter		Symbol	Rating	Unit
Input	Forward Current	I_F	± 50	mA
	Power Dissipation	P	70	mW
	Power dissipationDerating factor (above $T_a = 100^{\circ}\text{C}$)	PDD	2.9	mW/ $^{\circ}\text{C}$
	Thermal Resistance Junction-Ambient	R_{thJ-A}	325	$^{\circ}\text{C/W}$
	Thermal Resistance Junction-Case	R_{thJ-C}	200	$^{\circ}\text{C/W}$





output	Collector Power Dissipation	PC	150	mW
	Collector Current	IC	50	mA
	Collector-Emitter Voltage	VCEO	80	V
	Emitter - Collector Voltage	VECO	6	V
Total Power Dissipation		Ptot	200	mW
Isolation Voltage		Viso	5000	Vrms
Operating Temperature		Topr	-55~+110	°C
Storage Temperature		Tstg	-55~+125	°C
Soldering Temperature		Tsol	260 (10s)	°C

Electrical Characteristics (Ta=25°C)

Parameter		Symbol	Condition	Min.	Typ.	Max.	Unit
Input	Forward Voltage	VF	IF=±20mA	-	1.2	1.4	V
	Terminal Capacitance	Ct	V=0, f= 1kHz	-	30	250	pF
Output	Collector Dark Current	ICEO	VCE=20V	-	-	100	nA
	Collector-Emitter Breakdown Voltage	BVCEO	IC=0. 1mA, IF=0	80	-	-	V
	Emitter-Collector Breakdown Voltage	BVECO	IE= 10μA, IF=0	6	-	-	V
Transfer Characteristics	Current Transfer Ratio	CTR	IF=5mA, VCE=5V	50	-	150	%
	Collector-Emitter Saturation Voltage	VCE(sat)	IF=20mA, IC=1mA	-	0.1	0.2	V
	Isolation Resistance	RISO	DC500V, 40~60%R. H.	5x10 ¹⁰	1x10 ¹¹	-	Ω
	Isolation capacitance	Cf	V=0, f= 1MHz	-	0.6	1.0	pF
	Cut-off Frequency	Fc	VCE=5V, IC=2mA, RL= 100Ω, -3dB	-	80	-	kHz
switching time	Rise Time	Tr	VCE=2V, IC=2mA, RL= 100Ω	-	4	18	μs
	Fall Time	Tf		-	3	18	μs



Switching Time Test Circuit & Waveforms



Typical Characteristics

Figure 1. Forward Current vs Forward Voltage




Figure 2. Normalized Current Transfer Ratio vs Forward Current




Figure 3. Current Transfer Ratio vs Ambient Temperature




Figure 4. Dark Current vs Ambient Temperature






Figure 5. Collector Current vs Collector Voltage




Figure 6. Collector Current vs Collector Voltage




Figure 7. Collector-Emitter Saturation Voltage vs Collector Current





Figure 8. Switching Time vs Load Resistance





Temperature Profile Of Soldering

1. Soldering Precautions


Whether using a soldering iron or reflow soldering, the soldering temperature should be as close as possible to the conditions shown below.

•When reflow soldering

Reflow soldering should be completed within 10 seconds if reflow soldering does not exceed 260°C. The soldering temperature profile is based on the surface temperature of the plastisol (see the chart below, based on the surface temperature of the plastisol).

Reflow soldering is limited to one or two passes.

It must be used within 2 weeks after unpacking.




•Wave soldering

It is recommended to perform one-time soldering under temperature conditions.

Temperature: 260+0/-5°C Time: 10 sec.

Preheat temperature: 25 to 140°C Preheat time: 30 to 80 seconds.



• Soldering with a soldering iron

It is recommended to perform one-time soldering under temperature conditions.


Temperature: 260+0/-5°C; Time: 10 seconds.

Preheating temperature: 25 to 140°C; Preheating time: 30 to 80 seconds.



Outline Dimensions (mm)

DIP-4





Attention

- Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.
- HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.
- Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.