

WSTQ6080AN**Smart High-Side Power Switch Quad Channel, 80mΩ, DFN9×6-14L , AEC-Q100 qualified****Application**

- ◆ Suitable for resistive, inductive and capacitive loads
- ◆ Replaces electromechanical relays, fuses and discrete circuits
- ◆ Most suitable for loads with high inrush current, such as lamps
- ◆ Suitable for 12 V and 24 V trucks + trailer and transportation systems

Features

- ◆ PRO-SIL™ ISO 26262-ready for supporting the integrator in evaluation of hardware element according to ISO 26262:2018 Clause 8-13
- ◆ Quad channel device
- ◆ Very low stand-by current
- ◆ 3.3 V and 5 V compatible logic inputs
- ◆ Optimized electromagnetic compatibility
- ◆ Very low electromagnetic susceptibility

Diagnostic Functions


- ◆ Proportional load current sense
- ◆ High current sense precision for wide range currents
- ◆ Off-state open load detection
- ◆ OUT short to VS detection
- ◆ Overload and short to ground latch-off
- ◆ Thermal shutdown latch-off
- ◆ Very low current sense leakage

Protection Functions

- ◆ Undervoltage shutdown
- ◆ Overvoltage clamp
- ◆ Load current limitation
- ◆ Self limiting of fast thermal transients
- ◆ Protection against loss of ground and loss of VS
- ◆ Thermal shutdown
- ◆ Electrostatic discharge protection


Product Summary

Parameter	Symbol	Value
Max. transient supply voltage	V _S	60V
Operating voltage range	V _{NOM}	8-36V
On-state resistance (per channel, T _J = 25°C)	R _{ON}	80mΩ
Nominal load current (one channel active, T _J = 25°C)	I _{L(NOM)1}	3A
Nominal load current (All channels active, T _J = 25°C)	I _{L(NOM)2}	2A
Typical current sense ratio (I _{OUT} =1A)	K	820
Current limitation	I _{LIMH}	8.5A
Supply current in sleep	I _{SLEEP}	3uA

Package	DFN9×6-14L
Marking	WSTQ6080AN
	



Typical Application Circuit



Note1: The suggested GND diode is BAS21J.