



HEF4013(LX) Dual D-type Flip-Flop

Product Specification

Specification Revision History:

Version	Date	Description
2022-05-A1	2022-05	New
2023-04-B1	2023-04	Update the template



Contents

1、General Description.....	3
2、Block Diagram And Pin Description	5
2.1、Block Diagram	5
2.2、Pin Configurations.....	5
2.3、Pin Description.....	6
2.4、Function Table.....	6
3、Electrical Parameter	6
3.1、Absolute Maximum Ratings.....	6
3.2、Recommended Operating Conditions	7
3.3、Electrical Characteristics.....	7
3.3.1、DC Characteristics 1	7
3.3.2、DC Characteristics 2.....	8
3.3.3、AC Characteristics.....	9
4、Testing Circuit	10
4.1、AC Testing Circuit	10
4.2、AC Testing Waveforms.....	10
4.3、Measurement Points	11
4.4、Test Data	11
5、Package Information	12
5.1、SOP14	12
5.2、TSSOP14.....	13
6、Statements And Notes	14
6.1、The name and content of Hazardous substances or Elements in the product.....	14
6.2、Notes	14



1、General Description

The HEF4013 is a dual D-type flip-flop that features independent set-direct input (SD), clear-direct input (CD), clock input (CP) and outputs (Q, $\bar{Q}$). Data is accepted when CP is LOW and is transferred to the output on the positive-going edge of the clock. The active HIGH asynchronous CD and SD inputs are independent and override the D or CP inputs. The outputs are buffered for best system performance. The clock input's Schmitt-trigger action makes the circuit highly tolerant of slower clock rise and fall times. It operates over a recommended V_{DD} power supply range of 3V to 15V referenced to V_{SS} (usually ground). Unused inputs must be connected to V_{DD} , V_{SS} , or another input.

Features:

- Wide supply voltage range from 3V to 15V
- Fully static operation
- 5V, 10V, and 15V parametric ratings
- Standardized symmetrical output characteristics
- Tolerant of slow clock rise and fall times
- Specified from -40°C to +125°C
- Packaging information: SOP14/TSSOP14

**Ordering Information:****Reel packing specifications:**

Part number	Packaging form	Marking code	Reel quantity	Boxed reel quantity	Notes
HEF4013BT(LX)	SOP14	HEF4013BT	4000 PCS/reel	8000 PCS/box	Dimensions of plastic enclosure: 8.7mm×3.9mm Pin spacing: 1.27mm
HEF4013BTT(LX)	TSSOP14	HEF4013	5000 PCS/reel	10000 PCS/box	Dimensions of plastic enclosure: 5.0mm×4.4mm Pin spacing: 0.65mm

Note: If the physical information is inconsistent with the ordering information, please refer to the actual product.

2、Block Diagram And Pin Description

2.1、Block Diagram




Figure 1. Functional diagram





Figure 2. Logic diagram (one flip-flop)

2.2、Pin Configurations





2.3、Pin Description

Pin No.	Pin Name	Description
1	1Q	true output
2	1Q	complement output
3	1CP	clock input (LOW to HIGH edge-triggered)
4	1CD	asynchronous clear-direct input (active HIGH)
5	1D	data input
6	1SD	asynchronous set-direct input (active HIGH)
7	V _{SS}	ground (0V)
8	2SD	asynchronous set-direct input (active HIGH)
9	2D	data input
10	2CD	asynchronous clear-direct input (active HIGH)
11	2CP	clock input (LOW to HIGH edge-triggered)
12	2Q	complement output
13	2Q	true output
14	V _{DD}	supply voltage

2.4、Function Table

Input				Output	
nSD	nCD	nCP	nD	nQ	nQ
H	L	X	X	H	L
L	H	X	X	L	H
H	H	X	X	H	H
L	L	↑	L	L	H
L	L	↑	H	H	L

Note: H=HIGH voltage level; L=LOW voltage level; X=don't care; ↑=LOW-to-HIGH clock transition.

3、Electrical Parameter

3.1、Absolute Maximum Ratings

(Voltages are referenced to V_{SS} (ground=0V), unless otherwise specified.)

Parameter	Symbol	Conditions		Min.	Max.	Unit
supply voltage	V _{DD}	-		-0.5	+18	V
DC input current	I _{IK}	any one input		-	±10	mA
input voltage	V _I	all inputs		-0.5	V _{DD} +0.5	V
storage temperature	T _{stg}	-		-65	+150	°C
total power dissipation	P _{tot}	-		-	500	mW
device dissipation	P	per output transistor		-	100	mW
Soldering temperature	T _L	10s	SOP/TSSOP	260		°C



3.2、Recommended Operating Conditions

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
supply voltage	V_{DD}	-	3	-	15	V
ambient temperature	T_{amb}	in free air	-40	-	+125	°C
set-up time	t_{su}	$V_{DD}=5V$	40	-	-	ns
		$V_{DD}=10V$	20	-	-	ns
		$V_{DD}=15V$	15	-	-	ns
clock pulse width	t_{wCL}	$V_{DD}=5V$	140	-	-	ns
		$V_{DD}=10V$	60	-	-	ns
		$V_{DD}=15V$	40	-	-	ns
clock input frequency	f_{CL}	$V_{DD}=5V$	3.5	7	-	MHz
		$V_{DD}=10V$	8	16	-	MHz
		$V_{DD}=15V$	12	24	-	MHz
clock rise and fall time	t_{rCL}, t_{fCL}	$V_{DD}=5V$	-	-	15	us
		$V_{DD}=10V$	-	-	10	us
		$V_{DD}=15V$	-	-	5	us
Set or reset pulse width	$t_{wS/R}$	$V_{DD}=5V$	180	-	-	ns
		$V_{DD}=10V$	80	-	-	ns
		$V_{DD}=15V$	50	-	-	ns

Note: If more than one unit is cascaded in a parallel clocked operation, t_{rCL} must be made less than or equal to the sum of the fixed propagation delay time at 15pF and the transistion time of the output driving stage for the estimated capacitive load.

3.3、Electrical Characteristics

3.3.1、DC Characteristics 1

($T_{amb}=25^{\circ}C$, voltages are referenced to V_{SS} (ground=0V), unless otherwise specified.)

Parameter	Symbol	Conditions (V)			$T_{amb}=25^{\circ}C$			Unit
		V_O	V_{IN}	V_{DD}	Min.	Typ.	Max.	
supply current	I_{DD}	-	0, 5	5	-	-	1	uA
		-	0, 10	10	-	-	2	uA
		-	0, 15	15	-	-	4	uA
LOW-level output current	I_{OL}	0.4	0, 5	5	0.51	1	-	mA
		0.5	0, 10	10	1.3	2.6	-	mA
		1.5	0, 15	15	3.4	6.8	-	mA
HIGH-level output current	I_{OH}	4.6	0, 5	5	-0.51	-1	-	mA
		2.5	0, 5	5	-1.6	-3.2	-	mA
		9.5	0, 10	10	-1.3	-2.6	-	mA
		13.5	0, 15	15	-3.4	-6.8	-	mA
LOW-level output voltage	V_{OL}	-	0, 5	5	-	0	0.05	V
		-	0, 10	10	-	0	0.05	V
		-	0, 15	15	-	0	0.05	V
HIGH-level output voltage	V_{OH}	-	0, 5	5	4.95	5	-	V
		-	0, 10	10	9.95	10	-	V
		-	0, 15	15	14.95	15	-	V



LOW-level input voltage	V_{IL}	0.5, 4.5	-	5	-	-	1.5	V
		1, 9	-	10	-	-	3	V
		1.5, 13.5	-	15	-	-	4	V
HIGH-level input voltage	V_{IH}	0.5, 4.5	-	5	3.5	-	-	V
		1, 9	-	10	7	-	-	V
		1.5, 13.5	-	15	11	-	-	V
input leakage current	I_I	-	0, 15	15	-	-	± 1	μA

3.3.2、DC Characteristics 2

($T_{amb} = -40^{\circ}C$ to $+125^{\circ}C$, voltages are referenced to V_{SS} (ground=0V), unless otherwise specified.)

Parameter	Symbol	Conditions (V)			$T_{amb} = -40^{\circ}C$		$T_{amb} = +85^{\circ}C$		$T_{amb} = +125^{\circ}C$		Unit
		V_O	V_{IN}	V_{DD}	Min.	Max.	Min.	Max.	Min.	Max.	
supply current	I_{DD}	-	0, 5	5	-	1	-	30	-	30	μA
		-	0, 10	10	-	2	-	60	-	60	μA
		-	0, 15	15	-	4	-	120	-	120	μA
LOW-level output current	I_{OL}	0.4	0, 5	5	0.61	-	0.42	-	0.36	-	mA
		0.5	0, 10	10	1.5	-	1.1	-	0.9	-	mA
		1.5	0, 15	15	4	-	2.8	-	2.4	-	mA
HIGH-level output current	I_{OH}	4.6	0, 5	5	-0.61	-	-0.42	-	-0.36	-	mA
		2.5	0, 5	5	-1.8	-	-1.3	-	-1.15	-	mA
		9.5	0, 10	10	-1.5	-	-1.1	-	-0.9	-	mA
		13.5	0, 15	15	-4	-	-2.8	-	-2.4	-	mA
LOW-level output voltage	V_{OL}	-	0, 5	5	-	0.05	-	0.05	-	0.05	V
		-	0, 10	10	-	0.05	-	0.05	-	0.05	V
		-	0, 15	15	-	0.05	-	0.05	-	0.05	V
HIGH-level output voltage	V_{OH}	-	0, 5	5	4.95	-	4.95	-	4.95	-	V
		-	0, 10	10	9.95	-	9.95	-	9.95	-	V
		-	0, 15	15	14.95	-	14.95	-	14.95	-	V
LOW-level input voltage	V_{IL}	0.5, 4.5	-	5	-	1.5	-	1.5	-	1.5	V
		1, 9	-	10	-	3	-	3	-	3	V
		1.5, 13.5	-	15	-	4	-	4	-	4	V
HIGH-level input voltage	V_{IH}	0.5, 4.5	-	5	3.5	-	3.5	-	3.5	-	V
		1, 9	-	10	7	-	7	-	7	-	V
		1.5, 13.5	-	15	11	-	11	-	11	-	V
input leakage current	I_I	-	0, 15	15	-	± 1	-	± 1	-	± 1	μA



3.3.3、AC Characteristics

($T_{amb}=25^{\circ}\text{C}$, $V_{SS}=0\text{V}$, $t_r, t_f=20\text{ns}$, $C_L=50\text{pF}$, $R_L=20\text{k}\Omega$, unless otherwise specified.)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
HIGH to LOW propagation delay	t_{PHL}	nCP to nQ, $\bar{nQ}$; see Figure 4	$V_{DD}=5\text{V}$	-	150	300 ns
			$V_{DD}=10\text{V}$	-	65	130 ns
			$V_{DD}=15\text{V}$	-	45	90 ns
		nSD to $\bar{nQ}$ or nCD to nQ	$V_{DD}=5\text{V}$	-	200	400 ns
			$V_{DD}=10\text{V}$	-	85	170 ns
			$V_{DD}=15\text{V}$	-	60	120 ns
LOW to HIGH propagation delay	t_{PLH}	nCP to nQ, $\bar{nQ}$; see Figure 4	$V_{DD}=5\text{V}$	-	150	300 ns
			$V_{DD}=10\text{V}$	-	65	130 ns
			$V_{DD}=15\text{V}$	-	45	90 ns
		nSD to nQ or nCD to $\bar{nQ}$	$V_{DD}=5\text{V}$	-	150	300 ns
			$V_{DD}=10\text{V}$	-	65	130 ns
			$V_{DD}=15\text{V}$	-	45	90 ns
transition time	t_t	see Figure 4	$V_{DD}=5\text{V}$	-	100	200 ns
			$V_{DD}=10\text{V}$	-	50	100 ns
			$V_{DD}=15\text{V}$	-	40	80 ns
maximum clock frequency	$f_{clk(max)}$	see Figure 4	$V_{DD}=5\text{V}$	3.5	7	- MHz
			$V_{DD}=10\text{V}$	8	16	- MHz
			$V_{DD}=15\text{V}$	12	24	- MHz
pulse width	t_w	nCP input LOW; see Figure 4	$V_{DD}=5\text{V}$	-	70	140 ns
			$V_{DD}=10\text{V}$	-	30	60 ns
			$V_{DD}=15\text{V}$	-	20	40 ns
		nSD input HIGH or nCD input HIGH; see Figure 5	$V_{DD}=5\text{V}$	-	90	180 ns
			$V_{DD}=10\text{V}$	-	40	80 ns
			$V_{DD}=15\text{V}$	-	25	50 ns
set-up time	t_{su}	nD to nCP; see Figure 4	$V_{DD}=5\text{V}$	-	20	40 ns
			$V_{DD}=10\text{V}$	-	10	20 ns
			$V_{DD}=15\text{V}$	-	7	15 ns
hold time	t_h	nD to nCP; see Figure 4	$V_{DD}=5\text{V}$	-	2	5 ns
			$V_{DD}=10\text{V}$	-	2	5 ns
			$V_{DD}=15\text{V}$	-	2	5 ns
clock input rise or fall time	t_{rCL}, t_{fCL}	-	$V_{DD}=5\text{V}$	-	-	15 us
			$V_{DD}=10\text{V}$	-	-	10 us
			$V_{DD}=15\text{V}$	-	-	5 us
input capacitance	C_I	any input	-	5	7.5	pF

Note: t_t is the same as t_{TLH} and t_{THL} .

4、Testing Circuit

4.1、AC Testing Circuit




Figure 3. Test circuit for switching times

Definitions for test circuit:

DUT=Device Under Test.

C_L =Load capacitance including jig and probe capacitance.

R_T =Termination resistance should be equal to the output impedance Z_o of the pulse generator.

4.2、AC Testing Waveforms




Figure 4. Set-up time, hold time, minimum clock pulse width, propagation delays and transition times




Figure 5. nSD, nCD pulse width

4.3、Measurement Points

Supply voltage	Input	Output		
V_{DD}	V_M	V_M	V_X	V_Y
5V to 15V	$0.5 \times V_{DD}$	$0.5 \times V_{DD}$	$0.1 \times V_{DD}$	$0.9 \times V_{DD}$


4.4、Test Data

Supply voltage	Input		Load
V_{DD}	V_I	t_r, t_f	C_L
5V to 15V	V_{SS} or V_{DD}	$\leq 20\text{ns}$	50pF






5、Package Information

5.1、SOP14



Symbol	Dimensions (mm)	
	Min.	Max.
A	1.50	1.75
A1	0.05	0.25
A2	1.30	-
b	0.33	0.50
c	0.19	0.25
D	8.43	8.76
E	5.80	6.25
E1	3.75	4.00
e	1.27	
L	0.40	0.89
θ	0°	8°

5.2、TSSOP14



Symbol	Dimensions (mm)	
	Min.	Max.
A	-	1.20
A1	0.05	0.15
A2	0.80	1.05
b	0.19	0.30
c	0.09	0.20
D	4.90	5.10
E1	4.30	4.50
E	6.20	6.60
e	0.65	
L	0.45	0.75
L1	1.00	
θ	0 °	8 °



6、Statements And Notes

6.1、The name and content of Hazardous substances or Elements in the product

Part name	Hazardous substances or Elements									
	Lead and lead compounds	Mercury and mercury compounds	Cadmium and cadmium compounds	Hexavalent chromium compounds	Polybrominated biphenyls	Polybrominated biphenyl ethers	Dibutyl phthalate	Butylbenzyl phthalate	Di-2-ethylhexyl phthalate	Diisobutyl phthalate
Lead frame	○	○	○	○	○	○	○	○	○	○
Plastic resin	○	○	○	○	○	○	○	○	○	○
Chip	○	○	○	○	○	○	○	○	○	○
The lead	○	○	○	○	○	○	○	○	○	○
Plastic sheet installed	○	○	○	○	○	○	○	○	○	○
explanation	○: Indicates that the content of hazardous substances or elements in the detection limit of the following the SJ/T11363-2006 standard. ×: Indicates that the content of hazardous substances or elements exceeding the SJ/T11363-2006 Standard limit requirements.									

6.2、Notes

We Recommend you to read this chapter carefully before using this product.

The information in this chapter is provided for reference only and Lingxing disclaims any express or implied warranties, including but not limited to applicability, special application or non-infringement of third party rights.

This product is not suitable for critical equipment such as life-saving, life-sustaining or safety equipment. It is also not suitable for applications that may result in personal injury, death, or serious property or environmental damage due to product malfunction or failure. Lingxing will not be liable for any damages incurred by the customers at their own risk for such applications.

The customer is responsible for conducting all necessary tests Lingxing's application to avoid failure in the application or the application of the customer's third party users. Lingxing does not accept any liability.

The Company reserves the right to change or improve the information published in this chapter at any time. The information in this chapter are subject to change without notice. We recommend the customer to consult our sales staff before purchasing.

Please obtain related materials form Lingxing's regular channels and we are not responsible for its content if it is provided by sources other than our company.

In case of any conflict between the Chinese and English version, the version is subject to the Chinese one.