



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	H3	REVISED PER ECR-25-255998	15SEP2025	SA	DSC

1. WIRE INSULATION DIA 1.52[.060] TO 3.56[.140]
WIRE INSULATION DIA 3.81[.150] TO 5.59[.220]
2. TIN PLATE PER MIL SAE AS7928
3. PARTS MANUFACTURED AFTER MAY 2005 ARE ROHS COMPLIANT.



AMP WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
12-10 TO 22-16 AWG SOLID OR STRANDED	12-10 TO 22-16 AWG SOLID OR STRANDED	12-10 TO 22-16 AWG SOLID OR STRANDED

1 KIT = 50 PIECES	LOOSE PIECE	6-327639-0
50	LOOSE PIECE	327639
QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.S. GOULDEN 9-28-93		 TE Connectivity													
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 300V MAX		CHK R. HERSEY 9-28-93															
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] 0.26-0.96mm² [509-1,900] —				TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.20[.008] 3 PLC ± — 4 PLC ± — ANGLES ± —		APVD T. MICHIELUTTI 9-28-93		NAME SPLICE, BUTT, PIDG WIRE SIZE: 12-10 TO 22-18 AWG									
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL COPPER ASTM B-152 NYLON: COLOR-YELLOW		FINISH 		PRODUCT SPEC —		APPLICATION SPEC —		SIZE A3		CAGE CODE 00779		DRAWING NO C-327639		RESTRICTED TO —	
CUSTOMER DRAWING										SCALE 2:1		SHEET 1 OF 1		REV H3							