

SOD-123FL SURFACE MOUNT SILICON ZENER DIODES

Features

- Low Zener Impedance
- Power Dissipation of 1000mW
- High Stability and High Reliability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260°C

Applications

Zener diode is generally used as reference voltage sources in regulated power supplies or as protective diode in overvoltage protection circuits.



Mechanical Data

- Case: SOD-123FL
- Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750, Method 2026
- Polarity: Cathode line denotes the cathode end

Function Diagram

Zener Diode
3.3 to 330 Volts
Power Dissipation
1.0 Watts

SOD-123FL



Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	VALUE
Power Dissipation at Tc=75°C	P _D	mW	1000
Forward Voltage @ I _F =200mA	V _F	V	1.2
Storage Temperature	T _{stg}	°C	-55 ~+150
Junction Temperature	T _j	°C	-55 ~+150
Typical Thermal Resistance	R _{θJA}	°C /W	55

Electrical Parameter

SYMBOL	PARAMETER
V _Z	Reverse zener voltage @ I _{ZT}
I _{ZT}	Reverse current
Z _{ZT}	Maximum Zener Impedance @ I _{ZT}
I _{ZK}	Reverse Current
Z _{ZK}	Maximum Zener Impedance @ I _{ZK}
I _R	Reverse leakage current @ V _R
V _R	Reverse voltage
I _F	Forward current
V _F	Forward voltage @ I _F

MM1W3V3L THRU MM1W330L

SURFACE MOUNT ZENER DIODES

● Electrical Characteristics (Ta=25°C Unless otherwise noted)

Type Number	Type Code	Nominal Zener Voltage				Zener Impedance	Leakage Current $I_R@V_R$	
		V_Z			I_{ZT}	$Z_{ZT}@I_{ZT}$		
		Min.(V)	Nom.(V)	Max.(V)	(mA)	$Z_{ZT}(\Omega)$	$I_R(\mu A)$	$V_R(V)$
MM1W3V3L	FHD	3.10	3.3	3.50	75	10	100	1
MM1W3V6L	FHE	3.40	3.6	3.80	69	10	100	1
MM1W3V9L	FHF	3.70	3.9	4.10	64	9.0	50	1
MM1W4V3L	FHG	4.06	4.3	4.56	58	9.0	25	1
MM1W4V7L	FHJ	4.50	4.7	4.93	53	8.0	10	1
MM1W5V1L	FHK	4.84	5.1	5.36	49	7.0	10	1
MM1W5V6L	FHL	5.32	5.6	5.92	45	5.0	10	2
MM1W6V2L	FHN	5.86	6.2	6.51	41	2.0	10	3
MM1W6V8L	FHO	6.46	6.8	7.18	37	3.5	10	4
MM1W7V5L	FHQ	7.12	7.5	7.88	34	4.0	10	5
MM1W8V2L	FHR	7.79	8.2	8.67	31	4.5	10	6
MM1W9V1L	FHT	8.60	9.1	9.59	28	5.0	10	7
MM1W10L	FHU	9.50	10	10.5	25	7.0	10	7
MM1W11L	FHV	10.4	11	11.6	23	8.0	5	8
MM1W12L	FHW	11.4	12	12.6	21	9.0	5	9
MM1W13L	FHX	12.4	13	14.1	19	10	5	10
MM1W15L	FHZ	13.8	15	15.8	17	14	5	11
MM1W16L	FJA	15.2	16	17.1	16	16	5	12
MM1W18L	FJF	16.8	18	19.2	14	20	5	13
MM1W20L	FJG	19.0	20	21.2	13	22	5	15
MM1W22L	FJK	20.8	22	23.3	12	23	5	17
MM1W24L	FJL	22.8	24	26.0	11	25	5	18
MM1W27L	FJN	25.3	27	28.9	9.5	35	5	21
MM1W30L	FJQ	28.2	30	32.0	8.5	40	5	23
MM1W33L	FJR	31.3	33	34.9	7.5	45	5	25
MM1W36L	FJS	34.2	36	37.9	7.0	50	5	27
MM1W39L	FJT	37.2	39	41.5	6.5	60	5	30
MM1W43L	FLG	40.9	43	45.6	6.0	70	1	32
MM1W47L	FLJ	44.9	47	49.8	5.5	80	1	35
MM1W51L	FLK	48.6	51	54.0	5.0	95	1	38
MM1W56L	FLL	53.6	56	58.8	4.5	110	1	42
MM1W62L	FLN	58.9	62	65.6	4.0	125	1	47
MM1W68L	FLO	64.6	68	71.7	3.7	150	1	52

● Electrical Characteristics (Ta=25°C Unless otherwise noted)

Type Number	Type Code	Nominal Zener Voltage				Zener Impedance	Leakage Current $I_R@V_R$	
		V_Z			I_{ZT}	$Z_{ZT}@I_{ZT}$		
		Min.(V)	Nom.(V)	Max.(V)	(mA)	$Z_{ZT}(\Omega)$	$I_R(\mu A)$	$V_R(V)$
MM1W75L	FLQ	71.2	75	78.8	3.3	175	1	56
MM1W82L	FLR	77.9	82	87.0	3.0	200	1	62
MM1W91L	FLT	86.0	91	96.0	2.8	250	1	69
MM1W100L	FLU	95.0	100	105	2.5	350	1	76
MM1W110L	FLV	104	110	116	2.3	450	1	84
MM1W120L	FLW	114	120	127	2.0	550	1	91
MM1W135L	FLX	125	135	142	1.9	700	1	100
MM1W150L	FLZ	140	150	157	1.7	900	1	110
MM1W165L	FPA	155	165	172	1.6	1100	1	120
MM1W180L	FPF	170	180	191	1.4	1200	1	135
MM1W200L	FPG	189	200	211	1.2	1400	1	150
MM1W220L	FPK	209	220	231	1.0	1600	1	165
MM1W240L	FPL	229	240	251	1.0	1800	1	180
MM1W260L	FPM	249	260	271	1.0	2000	1	190
MM1W280L	FPN	269	280	291	1.0	2100	1	205
MM1W300L	FPQ	289	300	315	1.0	2300	1	230
MM1W330L	FLR	313	330	346	1.0	2500	1	250

● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




Fig. 1 Power Derating Curve




Fig.2 Typical Transient Thermal Impedance

MM1W3V3L THRU MM1W330L


SURFACE MOUNT ZENER DIODES

● Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SOD-123FL	R1	0.0169	3000	45000	180000	7"

● Package Outline Dimensions (SOD -123FL)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	0.90	1.10	0.035	0.430
B	2.55	2.85	0.100	0.111
C	1.60	1.90	0.063	0.074
D	3.60	3.90	0.031	0.043
E	1.00	1.20	0.031	0.035
F	0.40	0.90	0.047	0.055
G	0.10	0.25	0.003	0.007



● Suggested Pad Layout

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
J	1.00	-	0.040	-
K	-	1.90	-	0.074
M	1.50	-	0.059	-

