

GBP4005A THRU GBP410A

GBP 4.0 AMP Plastic-Encapsulate Bridge Rectifier

GBP Plastic-Encapsulate Bridge Rectifier

Features

- Ideal for printed circuit board
- Small size, simple installation
- High surge current capability
- Reliable low cost construction utilizing molded plastic technique
- High temperature soldering guaranteed: 260/10 seconds at 5lbs., (2.3kg) tension



Applications

General purpose 1 phase Bridgerectifier applications


Mechanical Data

- Case: GBP
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026
- Polarity: Cathode line denotes the cathode end

Function Diagram



Reverse Voltage
50-1000 V
Forward Current
4.0 Ampere



Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	GBP4005A	GBP401A	GBP402A	GBP404A	GBP406A	GBP408A	GBP410A
Device marking code			GBP4005A	GBP401A	GBP402A	GBP404A	GBP406A	GBP408A	GBP410A
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	V	50	100	200	400	600	800	1000
Maximum RMS Voltage	V_{RMS}	V	35	70	140	280	420	560	700
Maximum DC blocking Voltage	V_{DC}	V	50	100	200	400	600	800	1000
Maximum Average Forward Rectified Current @60Hz sinewave, Resistance load,TL (Fig.1)	$I_{F(AV)}$	A	4.0						
Non-repetitive Peak Forward Surge Current @ t=8.3ms Half-sine wave	I_{FSM}	A	135						
Rating for fusing (t=8.3ms, Ta=25 °C)	I^2t	A ² S	75.63						
Storage temperature	T_{stg}	°C	-55 ~ +150						
Junction temperature	T_j	°C	-55 ~ +150						
Typical Thermal Resistance	$R_{\theta J-A}$	°C /W	45						
	$R_{\theta J-L}$	°C /W	10						





GBP4005A THRU GBP410A

GBP 4.0 AMP Plastic-Encapsulate Bridge Rectifier

Electrical Characteristics (Ta=25°C Unless otherwise noted)

PARAMETER	TEST CONDITIONS	SYMBOL	UNIT	GBP4005A	GBP401A	GBP402A	GBP404A	GBP406A	GBP408A	GBP410A
Maximum instantaneous forward voltage	$I_F=4.0A$	V_F	V	1.1						
Maximum DC reverse current at rated DC blocking voltage	$V_R=V_{DC}, T_A=25^{\circ}C$	I_{R1}	μA	10						
	$V_R=V_{DC}, T_A=100^{\circ}C$	I_{R2}		1000						
Typical junction capacitance	4.0V DC, 1MHz	C_J	pF	35						

Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



GBP4005A THRU GBP410A

GBP 4.0 AMP Plastic-Encapsulate Bridge Rectifier

● Ordering Information

PACKAGE	UNIT WEIGHT(g)	BOX(pcs)	CARTON(pcs)
GBP	1.25	500	5000

● Package Outline Dimensions (GBP)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	13.80	14.20	0.543	0.560
B	10.40	10.80	0.409	0.425
C	1.80	2.20	0.071	0.086
D	12.70	13.7	0.500	0.540
E	1.30	1.50	0.051	0.059
F	0.77	0.79	0.030	0.031
G	3.60	4.00	0.142	0.157
H	3.00	3.40	0.118	0.133
I	0.80	1.10	0.031	0.043
J	0.30	0.40	0.012	0.016