

Specification for approval

客户名称:

(Customer Name)

产品名称:

DC-LINK直流薄膜电容器

(Product Name)

DC-LINK DC Thin Film Capacitor

客户料号:

(Customer part number)

科尼盛料号:

228CB0115

(KNSCHA number)

型号规格:

DC-LINK 9 $\mu$ F/1000V P=27.5mm 32\*37\*22mm  
L=5.5mm $\pm$ 0.5mm/0.8CU铜线\*2PIN

(Specifications)

日期:

2025.10.1

DATE

|                    |                 |
|--------------------|-----------------|
| 制 造<br>Manufacture |                 |
| 核 准<br>APPROVAL    | 制 作<br>PREPARED |
| 王师                 | 张优美             |

|                            |                |                 |
|----------------------------|----------------|-----------------|
| 客户承认栏<br>CUSTOMER APPROVED |                |                 |
| 核 准<br>APPROVED            | 确 认<br>CHECKED | 经 办<br>DESIGNED |
|                            |                |                 |

**广东科尼盛电子科技有限公司**

KNSCHA ELECTRONICS CO.,LIMITED

地址: 广东省东莞市东坑镇汇金展拓科技园 A2-A3栋


Buildings A2-A3, Huijin Zhantuo Science and Technology Park,  
Dongkeng Town, Dongguan City, Guangdong Province

TEL:0769-83698067 81035570 FAX: 0769-83861559

Email: sales@knscha.com Website: <http://www.knscha.com>



|                                                             |       |                                                 |
|-------------------------------------------------------------|-------|-------------------------------------------------|
| capacitor                                                   | 物料编码  | 228CB0115                                       |
| <u>main data</u>                                            |       |                                                 |
| 额定容量 C <sub>n</sub><br>Rated Capacitance                    | [ μF] | 9                                               |
| 容量偏差<br>Capacitance tolerance                               | [%]   | ±10                                             |
| 额定电压 U <sub>n</sub><br>Rated Voltage                        | [Vdc] | 1000                                            |
| 损耗 tg δ<br>Tangent of loss angle                            |       | ≤15x10 <sup>-4</sup> (1kHz, 20℃)                |
| 最大电流 I <sub>max</sub><br>Maximum current                    | [A]   | 18.38                                           |
| 等效串联电阻 ESR                                                  | mΩ    | ≤4.4 (1kHz)                                     |
| 最大峰值电流 Î<br>Maximum peak current Î                          | [A]   | 675                                             |
| 电压变化率 dv/dt                                                 | v/ μs | 75                                              |
| 预期寿命                                                        |       | 100000h @U <sub>n</sub> , θ <sub>amb</sub> ≤70℃ |
| 极间测试 U <sub>test</sub><br>Test voltage terminal to terminal | [Vdc] | 1500 - 10s                                      |
| 绝缘电阻 IR×CN<br>Insulation Resistance                         |       | ≥100000s (20℃ , 100VDC, 60s)                    |
| 运行温度 θ <sub>amb</sub><br>Operating Temperature              | [℃]   | -40 / +85                                       |
| 线径 D                                                        | [mm]  | 2-0.8                                           |
| 长度 L                                                        | [mm]  | 32                                              |
| 宽度 W                                                        | [mm]  | 22                                              |
| 高度 H                                                        | [mm]  | 37                                              |
| 中心距 P                                                       | [mm]  | 27.5                                            |
| 绝缘介质<br>insulation medium                                   |       | 聚丙烯薄膜Polypropylene film                         |
| 填充介质<br>Filling medium                                      |       | 环氧树脂 epoxy                                      |



|                                |            |                      |                 |                                                      |      |            |             |
|--------------------------------|------------|----------------------|-----------------|------------------------------------------------------|------|------------|-------------|
|                                |            |                      |                 |                                                      |      |            |             |
| remark                         | designer   | Revision Description |                 |                                                      |      | Changed by | change date |
| Design                         | xia. zhang | 2025. 10. 01         | Outline drawing | proportion                                           | 1: 1 | edition    | A           |
| auditing standard              |            |                      |                 | <b>KNSCHA</b><br><b>9μF±10%1000VDC</b><br><b>MPD</b> |      |            |             |
| approved                       |            |                      |                 |                                                      |      |            |             |
| KNSCHA ELECTRONICSCO., LIMITED |            |                      |                 |                                                      |      |            |             |