



自主封測 品質把控 售後保障


WEB | WWW.TDSEMIC.COM




電源管理




顯示驅動




二三極管




LDO穩壓器




觸摸芯片




MOS管




運算放大器



存儲芯片



MCU



串口通信

3401AJ-TD

產品規格說明書

General Description



- Advanced Trench Technology
- Excellent $R_{DS(ON)}$ and Low Gate Charge

Features

- 30V, 4A
- $R_{DS(ON)} < 47m\Omega @ V_{GS} = 10V$
- $R_{DS(ON)} < 52m\Omega @ V_{GS} = 4.5V$
- $R_{DS(ON)} < 62m\Omega @ V_{GS} = 2.5V$

Applications

- Load Switch
- PWM Application
- Power Management



Absolute Maximum Ratings (@ $T_A = 25^{\circ}C$ unless otherwise specified)

Symbol	Parameter		Value	Units
V_{DS}	Drain-to-Source Voltage		30	V
V_{GS}	Gate-to-Source Voltage		± 12	V
I_D	Continuous Drain Current	$T_A = 25^{\circ}C$	4	A
		$T_A = 100^{\circ}C$	3	
I_{DM}	Pulsed Drain Current ⁽¹⁾		16	A
P_D	Power Dissipation	$T_A = 25^{\circ}C$	1.2	W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient ⁽²⁾		103	$^{\circ}C/W$
T_J, T_{STG}	Junction & Storage Temperature Range		-55 to 150	$^{\circ}C$

Electrical Characteristics (T_J = 25°C unless otherwise specified)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
Off Characteristics						
V _{(BR)DSS}	Drain-Source Breakdown Voltage	I _D = 250μA, V _{GS} = 0V	30	-	-	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 30V, V _{GS} = 0V	-	-	1.0	μA
I _{GSS}	Gate-Body Leakage Current	V _{DS} = 0V, V _{GS} = ±12V	-	-	±100	nA
On Characteristics						
V _{GS(th)}	Gate Threshold Voltage	V _{DS} = V _{GS} , I _D = 250μA	0.5	1.0	1.4	V
R _{DS(ON)}	Static Drain-Source ON-Resistance ⁽³⁾	V _{GS} = 10V, I _D = 4A	-	45	47	mΩ
		V _{GS} = 4.5V, I _D = 3A	-	48	52	mΩ
		V _{GS} = 2.5V, I _D = 2A	-	58	62	mΩ
Dynamic Characteristics						
C _{iss}	Input Capacitance	V _{GS} = 0V, V _{DS} = 15V, f = 1MHz	-	414	-	pF
C _{oss}	Output Capacitance		-	36	-	pF
C _{rss}	Reverse Transfer Capacitance		-	29	-	pF
Q _g	Total Gate Charge	V _{GS} = 0 to 4.5V V _{DS} = 15V, I _D = 2A	-	4.5	-	nC
Q _{gs}	Gate Source Charge		-	1	-	nC
Q _{gd}	Gate Drain("Miller") Charge		-	1	-	nC
Switching Characteristics						
t _{d(on)}	Turn-On DelayTime	V _{GS} = 4.5V, V _{DD} = 15V I _D = 2A, R _{GEN} = 3Ω	-	4	-	ns
t _r	Turn-On Rise Time		-	13	-	ns
t _{d(off)}	Turn-Off DelayTime		-	41	-	ns
t _f	Turn-Off Fall Time		-	17	-	ns
Drain-Source Diode Characteristics and Max Ratings						
I _S	Maximum Continuous Drain to Source Diode Forward Current		-	-	4	A
I _{SM}	Maximum Pulsed Drain to Source Diode Forward Current		-	-	16	A
V _{SD}	Drain to Source Diode Forward Voltage	V _{GS} = 0V, I _S = 4A	-	-	1.2	V
trr	Body Diode Reverse Recovery Time	I _F = 2A, di/dt = 100A/us	-	6	-	ns
Qrr	Body Diode Reverse Recovery Charge		-	1	-	nC

- Notes:
1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature.
 2. R_{θJA} is measured with the device mounted on a 1inch² pad of 2oz copper FR4 PCB
 3. Pulse Test: Pulse Width ≤ 300μs, Duty Cycle ≤ 0.5%.

Test Circuit




Figure 1: Gate Charge Test Circuit & Waveform




Figure 2: Resistive Switching Test Circuit & Waveform




Figure 3: Unclamped Inductive Switching Test Circuit & Waveform





Figure 4: Diode Recovery Test Circuit & Waveform

Package Mechanical Data(SOT-23)



SYMBOL	MILLIMETER		
	MIN	NOM	MAX
A	0.95	1.00	1.05
A1	0.01	0.05	0.10
A2	0.35	0.40	0.45
b	0.11 BSC		
c	2.80	2.90	3.00
D	2.30	2.40	2.50
E	1.20	1.30	1.40
E1	1.90 BSC		
L	0.20	-	-
L1	0.30	0.40	0.50
A2	0.60 REF		